

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315136

Luminaire Tested: **LDA2B20NFL8035D010 PINW1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315136
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B20NFL8035D010 PINW1MW
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, Black oculus, matte white finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1857.1 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315136

CATALOG NUMBER: LDA2B20NFL8035D010 PINW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P315136

CATALOG NUMBER: LDA2B20NFL8035D010 PINW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																											
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97									97																											
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94									94																											
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91									91																											
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89									89																											
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86									86																											
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84									84																											
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82									82																											
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80									80																											
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78									78																											
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76									76																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4753343
5°	4383723
10°	2954086
15°	1456499
20°	622102
25°	244583
30°	96277
35°	42220
40°	20287
45°	9768
50°	5373
55°	3011
60°	1776
65°	1051
70°	1298
75°	0
80°	0
85°	0



TEST NUMBER: P315136

CATALOG NUMBER: LDA2B20NFL8035D010 PINW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	749.8	40.4
10°-20°	807.5	43.5
20°-30°	233.2	12.6
30°-40°	49.2	2.6
40°-50°	12.1	0.7
50°-60°	3.5	0.2
60°-70°	1.2	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1790.5	96.4
0°-40°	1839.7	99.1
0°-60°	1855.3	99.9
0°-90°	1857.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1857.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9635	
5°	8852	750
15°	2852	808
25°	449	233
35°	70	49
45°	14	12
55°	4	3
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P315136

CATALOG NUMBER: LDA2B20NFL8035D010 PINW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9634.6
1°	9574.1
2°	9471.7
3°	9333.3
4°	9137.1
5°	8851.6
6°	8466.3
7°	7963.6
8°	7345.3
9°	6624.5
10°	5896.7
11°	5161.0
12°	4466.5
13°	3850.0
14°	3307.9
15°	2851.6
17.5°	1884.7
20°	1184.9
22.5°	728.7
25°	449.3
27.5°	274.1
30°	169.0
32.5°	106.8
35°	70.1
37.5°	46.4
40°	31.5
42.5°	21.9
45°	14.0
47.5°	8.8
50°	7.0
52.5°	5.3
55°	3.5
57.5°	2.6
60°	1.8
62.5°	1.8
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.9
80°	0.0
82.5°	0.0



TEST NUMBER: P315136

CATALOG NUMBER: LDA2B20NFL8035D010 PINW1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)