

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492357

Luminaire Tested: **LDA2B058040R60D010 2LBD1GPH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058040R60D010 2LBD1GPH
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 807.7 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492357

CATALOG NUMBER: LDA2B058040R60D010 2LBD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P492357

CATALOG NUMBER: LDA2B058040R60D010 2LBD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54	62	57	54	61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	483593
5°	459093
10°	449423
15°	435019
20°	397706
25°	353129
30°	264163
35°	149125
40°	56160
45°	25118
50°	12281
55°	2494
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P492357

CATALOG NUMBER: LDA2B058040R60D010 2LBD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.8	10.9
10°-20°	236.5	29.3
20°-30°	289.0	35.8
30°-40°	157.6	19.5
40°-50°	31.5	3.9
50°-60°	4.5	0.6
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.3	75.9
0°-40°	770.9	95.4
0°-60°	807.0	99.9
0°-90°	807.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	807.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	980	
5°	927	88
15°	852	237
25°	649	289
35°	248	158
45°	36	32
55°	3	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492357

CATALOG NUMBER: LDA2B058040R60D010 2LBD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	980.2
1°	975.7
2°	967.1
3°	955.6
4°	939.2
5°	927.0
6°	920.4
7°	912.6
8°	906.5
9°	903.6
10°	897.1
11°	889.7
12°	883.2
13°	875.4
14°	863.9
15°	851.7
16°	836.1
17°	814.4
18°	800.5
19°	778.0
20°	757.5
21°	738.7
22.5°	707.2
23°	694.1
24°	674.0
25°	648.7
26°	616.3
27°	582.4
28°	543.5
29°	506.7
30°	463.7
32.5°	355.6
35°	247.6
37.5°	155.1
40°	87.2
42.5°	54.4
45°	36.0
47.5°	24.6
50°	16.0
52.5°	8.2
55°	2.9
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.4



TEST NUMBER: P492357

CATALOG NUMBER: LDA2B058040R60D010 2LBD1GPH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)