

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279922

Luminaire Tested: **LDA2B208040D010 EU2B20FL408040 2LBAD1H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279922  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B208040D010 EU2B20FL408040 2LBAD1H  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl, Self-Flanged, H  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2268.1 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279922

CATALOG NUMBER: LDA2B208040D010 EU2B20FL408040 2LBAD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P279922

CATALOG NUMBER: LDA2B208040D010 EU2B20FL408040 2LBAD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89						89													
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69						69													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3118787
5°	3052847
10°	2782452
15°	2173615
20°	1286888
25°	478388
30°	149485
35°	66492
40°	30849
45°	14513
50°	7982
55°	4473
60°	2072
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P279922

CATALOG NUMBER: LDA2B208040D010 EU2B20FL408040 2LBAD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	569.8	25.1
10°-20°	1133.1	50.0
20°-30°	464.1	20.5
30°-40°	76.8	3.4
40°-50°	18.2	0.8
50°-60°	4.8	0.2
60°-70°	1.1	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2167.0	95.5
0°-40°	2243.8	98.9
0°-60°	2266.8	99.9
0°-90°	2268.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2268.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6322	
5°	6164	570
15°	4256	1133
25°	879	464
35°	110	77
45°	21	18
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279922

CATALOG NUMBER: LDA2B208040D010 EU2B20FL408040 2LBAD1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6321.5
1°	6299.6
2°	6270.5
3°	6244.4
4°	6210.1
5°	6164.3
6°	6096.6
7°	6008.1
8°	5882.1
9°	5729.0
10°	5554.1
11°	5351.0
12°	5122.0
13°	4860.6
14°	4570.1
15°	4255.6
17.5°	3374.7
20°	2451.1
22.5°	1569.2
25°	878.8
27.5°	463.4
30°	262.4
32.5°	166.6
35°	110.4
37.5°	72.9
40°	47.9
42.5°	31.2
45°	20.8
47.5°	14.6
50°	10.4
52.5°	7.3
55°	5.2
57.5°	3.1
60°	2.1
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279922

CATALOG NUMBER: LDA2B208040D010 EU2B20FL408040 2LBAD1H

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)