

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492377

Luminaire Tested: **LDA2B058040R60D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492377
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058040R60D010 2LBDLC1MMS
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 807.6 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492377

CATALOG NUMBER: LDA2B058040R60D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P492377

CATALOG NUMBER: LDA2B058040R60D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	478068
5°	465581
10°	452729
15°	430320
20°	393191
25°	337615
30°	251231
35°	147499
40°	70265
45°	32793
50°	16348
55°	5763
60°	1283
65°	1051
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P492377

CATALOG NUMBER: LDA2B058040R60D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.5	11.0
10°-20°	234.4	29.0
20°-30°	278.3	34.5
30°-40°	157.1	19.5
40°-50°	40.8	5.1
50°-60°	7.4	0.9
60°-70°	0.8	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	601.2	74.4
0°-40°	758.4	93.9
0°-60°	806.6	99.9
0°-90°	807.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	807.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	969	
5°	940	88
15°	842	234
25°	620	278
35°	245	157
45°	47	41
55°	7	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492377

CATALOG NUMBER: LDA2B058040R60D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	969.0
1°	969.4
2°	962.7
3°	957.0
4°	945.9
5°	940.1
6°	929.9
7°	922.4
8°	915.3
9°	910.4
10°	903.7
11°	890.9
12°	878.9
13°	872.2
14°	856.7
15°	842.5
16°	826.1
17°	806.6
18°	787.9
19°	765.8
20°	748.9
21°	725.8
22.5°	687.7
23°	681.0
24°	648.6
25°	620.2
26°	588.7
27°	552.4
28°	516.4
29°	481.4
30°	441.0
32.5°	339.4
35°	244.9
37.5°	167.3
40°	109.1
42.5°	71.4
45°	47.0
47.5°	31.9
50°	21.3
52.5°	13.3
55°	6.7
57.5°	2.7
60°	1.3
62.5°	0.9
65°	0.9



TEST NUMBER: P492377

CATALOG NUMBER: LDA2B058040R60D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)