

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279923

Luminaire Tested: **LDA2B208040D010 EU2B20FL408040 2LBAD1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279923  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B208040D010 EU2B20FL408040 2LBAD1LI  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl, Self-Flanged, LI  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2285.6 lumens  
Efficiency: N/A  
Efficacy: 111.0 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279923

CATALOG NUMBER: LDA2B208040D010 EU2B20FL408040 2LBAD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P279923

CATALOG NUMBER: LDA2B208040D010 EU2B20FL408040 2LBAD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																				
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																				
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																																				
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																																				
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82																																				
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																																				
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																																				
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																				
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																																				
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3142912
5°	3076470
10°	2803994
15°	2190470
20°	1296863
25°	482089
30°	150625
35°	66974
40°	31107
45°	14652
50°	8059
55°	4473
60°	2072
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P279923

CATALOG NUMBER: LDA2B208040D010 EU2B20FL408040 2LBAD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	574.2	25.1
10°-20°	1141.9	50.0
20°-30°	467.7	20.5
30°-40°	77.4	3.4
40°-50°	18.3	0.8
50°-60°	4.8	0.2
60°-70°	1.1	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2183.8	95.5
0°-40°	2261.2	98.9
0°-60°	2284.4	99.9
0°-90°	2285.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2285.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6370	
5°	6212	574
15°	4289	1142
25°	886	468
35°	111	77
45°	21	18
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279923

CATALOG NUMBER: LDA2B208040D010 EU2B20FL408040 2LBAD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6370.4
1°	6348.4
2°	6319.0
3°	6292.8
4°	6258.2
5°	6212.0
6°	6143.8
7°	6054.6
8°	5927.6
9°	5773.4
10°	5597.1
11°	5392.5
12°	5161.6
13°	4898.2
14°	4605.5
15°	4288.6
17.5°	3400.9
20°	2470.1
22.5°	1581.3
25°	885.6
27.5°	466.9
30°	264.4
32.5°	167.9
35°	111.2
37.5°	73.5
40°	48.3
42.5°	31.5
45°	21.0
47.5°	14.7
50°	10.5
52.5°	7.3
55°	5.2
57.5°	3.1
60°	2.1
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279923

CATALOG NUMBER: LDA2B208040D010 EU2B20FL408040 2LBAD1LI

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)