

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492422

Luminaire Tested: **LDA2B058040R70D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058040R70D010 2LBDLC1MB
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 802.4 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492422

CATALOG NUMBER: LDA2B058040R70D010 2LBDLC1MB

Luminous Intensity Polar Plot





TEST NUMBER: P492422

CATALOG NUMBER: LDA2B058040R70D010 2LBDLC1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	47	66	57	50	46	56	50	46	55	50	46	54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	317725
5°	315868
10°	313759
15°	307941
20°	296796
25°	284158
30°	270714
35°	223327
40°	145166
45°	75842
50°	35307
55°	12902
60°	1283
65°	1051
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P492422

CATALOG NUMBER: LDA2B058040R70D010 2LBDLC1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.3	7.5
10°-20°	169.4	21.1
20°-30°	240.5	30.0
30°-40°	224.9	28.0
40°-50°	90.4	11.3
50°-60°	15.8	2.0
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	470.2	58.6
0°-40°	695.1	86.6
0°-60°	801.3	99.9
0°-90°	802.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	802.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	644	
5°	638	60
15°	603	169
25°	522	240
35°	371	225
45°	109	90
55°	15	16
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492422

CATALOG NUMBER: LDA2B058040R70D010 2LBDLC1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	644.0
1°	644.9
2°	643.6
3°	640.9
4°	639.6
5°	637.8
6°	630.7
7°	633.0
8°	626.8
9°	625.4
10°	626.3
11°	620.6
12°	619.3
13°	612.2
14°	609.5
15°	602.9
16°	598.9
17°	591.0
18°	581.7
19°	576.4
20°	565.3
21°	556.9
22.5°	541.5
23°	537.5
24°	530.0
25°	522.0
26°	515.8
27°	507.0
28°	498.1
29°	487.5
30°	475.2
32.5°	431.8
35°	370.8
37.5°	298.8
40°	225.4
42.5°	160.9
45°	108.7
47.5°	71.6
50°	46.0
52.5°	28.7
55°	15.0
57.5°	4.9
60°	1.3
62.5°	0.9
65°	0.9



TEST NUMBER: P492422

CATALOG NUMBER: LDA2B058040R70D010 2LBDLC1MB

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)