

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279033

Luminaire Tested: **LDA2B208040D010 EU2B20NFL258040 2LBAD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208040D010 EU2B20NFL258040 2LBAD1GPH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in ADJ spun Refl, Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2207.7 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279033

CATALOG NUMBER: LDA2B208040D010 EU2B20NFL258040 2LBAD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P279033

CATALOG NUMBER: LDA2B208040D010 EU2B20NFL258040 2LBAD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5650966
5°	5211576
10°	3511969
15°	1731547
20°	739602
25°	290745
30°	114450
35°	50170
40°	24151
45°	11652
50°	6371
55°	3613
60°	2072
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P279033

CATALOG NUMBER: LDA2B208040D010 EU2B20NFL258040 2LBAD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	891.4	40.4
10°-20°	960.0	43.5
20°-30°	277.2	12.6
30°-40°	58.5	2.7
40°-50°	14.4	0.7
50°-60°	4.1	0.2
60°-70°	1.4	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2128.6	96.4
0°-40°	2187.1	99.1
0°-60°	2205.6	99.9
0°-90°	2207.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2207.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11454	
5°	10523	891
15°	3390	960
25°	534	277
35°	83	59
45°	17	14
55°	4	4
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P279033

CATALOG NUMBER: LDA2B208040D010 EU2B20NFL258040 2LBAD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	11454.0
1°	11382.2
2°	11260.4
3°	11095.9
4°	10862.6
5°	10523.2
6°	10065.1
7°	9467.5
8°	8732.4
9°	7875.5
10°	7010.3
11°	6135.7
12°	5310.0
13°	4577.0
14°	3932.5
15°	3390.1
17.5°	2240.6
20°	1408.7
22.5°	866.3
25°	534.1
27.5°	325.9
30°	200.9
32.5°	127.0
35°	83.3
37.5°	55.2
40°	37.5
42.5°	26.0
45°	16.7
47.5°	10.4
50°	8.3
52.5°	6.2
55°	4.2
57.5°	3.1
60°	2.1
62.5°	2.1
65°	1.0
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	1.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279033

CATALOG NUMBER: LDA2B208040D010 EU2B20NFL258040 2LBAD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)