

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278371

Luminaire Tested: **LDA2B058050D010 EU2B05NFL258050 2LBAD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278371
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B058050D010 EU2B05NFL258050 2LBAD1LI
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl, Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 872.1 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278371

CATALOG NUMBER: LDA2B058050D010 EU2B05NFL258050 2LBAD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P278371

CATALOG NUMBER: LDA2B058050D010 EU2B05NFL258050 2LBAD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97		
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94		
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91		
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89		
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86		
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84		
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82		
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80		
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78		
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2232363
5°	2058789
10°	1387344
15°	684017
20°	292176
25°	114861
30°	45233
35°	19815
40°	9532
45°	4605
50°	2533
55°	1376
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P278371

CATALOG NUMBER: LDA2B058050D010 EU2B05NFL258050 2LBAD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.1	40.4
10°-20°	379.2	43.5
20°-30°	109.5	12.6
30°-40°	23.1	2.7
40°-50°	5.7	0.7
50°-60°	1.6	0.2
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	840.9	96.4
0°-40°	864.0	99.1
0°-60°	871.3	99.9
0°-90°	872.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	872.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4525	
5°	4157	352
15°	1339	379
25°	211	109
35°	33	23
45°	7	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278371

CATALOG NUMBER: LDA2B058050D010 EU2B05NFL258050 2LBAD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4524.8
1°	4496.4
2°	4448.3
3°	4383.3
4°	4291.2
5°	4157.1
6°	3976.1
7°	3740.0
8°	3449.6
9°	3111.1
10°	2769.3
11°	2423.8
12°	2097.7
13°	1808.1
14°	1553.5
15°	1339.2
17.5°	885.1
20°	556.5
22.5°	342.2
25°	211.0
27.5°	128.7
30°	79.4
32.5°	50.2
35°	32.9
37.5°	21.8
40°	14.8
42.5°	10.3
45°	6.6
47.5°	4.1
50°	3.3
52.5°	2.5
55°	1.6
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P278371

CATALOG NUMBER: LDA2B058050D010 EU2B05NFL258050 2LBAD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)