

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278218

Luminaire Tested: **LDA2B208040D010 EU2B20SP158040 2LBAD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278218
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208040D010 EU2B20SP158040 2LBAD1H
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2107.8 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278218

CATALOG NUMBER: LDA2B208040D010 EU2B20SP158040 2LBAD1H

Luminous Intensity Polar Plot





TEST NUMBER: P278218

CATALOG NUMBER: LDA2B208040D010 EU2B20SP158040 2LBAD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98			
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96			
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93			
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92			
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90			
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88			
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86			
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85			
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83			
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9522327
5°	7591780
10°	3295949
15°	1138752
20°	466904
25°	210887
30°	84826
35°	39510
40°	21446
45°	8024
50°	4759
55°	3613
60°	2072
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P278218

CATALOG NUMBER: LDA2B208040D010 EU2B20SP158040 2LBAD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1158.5	55.0
10°-20°	695.8	33.0
20°-30°	191.5	9.1
30°-40°	45.5	2.2
40°-50°	11.2	0.5
50°-60°	3.7	0.2
60°-70°	1.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2045.8	97.1
0°-40°	2091.4	99.2
0°-60°	2106.3	99.9
0°-90°	2107.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2107.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19301	
5°	15329	###
15°	2230	696
25°	387	192
35°	66	46
45°	12	11
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278218

CATALOG NUMBER: LDA2B208040D010 EU2B20SP158040 2LBAD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	19300.9
1°	19087.5
2°	18576.2
3°	17796.2
4°	16695.5
5°	15329.3
6°	13661.1
7°	11833.6
8°	9913.4
9°	8147.3
10°	6579.1
11°	5251.4
12°	4179.9
13°	3370.8
14°	2727.2
15°	2229.5
17.5°	1383.9
20°	889.3
22.5°	583.1
25°	387.4
27.5°	248.9
30°	148.9
32.5°	93.7
35°	65.6
37.5°	47.9
40°	33.3
42.5°	19.8
45°	11.5
47.5°	8.3
50°	6.2
52.5°	5.2
55°	4.2
57.5°	3.1
60°	2.1
62.5°	2.1
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P278218

CATALOG NUMBER: LDA2B208040D010 EU2B20SP158040 2LBAD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)