

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492426

Luminaire Tested: **LDA2B058050R20D010 2LBD1B**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P492426  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B058050R20D010 2LBD1B  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 833.8 lumens  
Efficiency: N/A  
Efficacy: 119.1 lumens/watt  
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P492426  
CATALOG NUMBER: LDA2B058050R20D010 2LBD1B

### Luminous Intensity Polar Plot





TEST NUMBER: P492426

CATALOG NUMBER: LDA2B058050R20D010 2LBD1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	116	114	112	110	113	111	110	109	108	106	105	105	104	103	102	102	101	100	99	99	98	98	98	98
2	112	109	106	104	110	107	105	103	104	102	101	101	102	100	99	99	99	98	97	97	97	96	95	95
3	109	105	102	100	108	104	101	99	102	99	97	97	99	97	96	96	97	96	94	94	94	93	92	92
4	107	102	99	96	105	101	98	95	99	96	94	94	97	95	93	93	96	94	92	92	92	91	90	90
5	104	99	95	93	103	98	95	92	97	94	92	92	95	93	91	91	94	92	90	90	90	89	88	88
6	102	96	93	90	101	96	92	90	95	92	89	89	93	91	89	89	92	90	88	88	88	87	86	86
7	100	94	91	88	99	94	90	88	92	90	87	87	92	89	87	87	91	88	87	87	87	86	85	85
8	98	92	88	86	97	91	88	86	91	88	86	86	90	87	85	85	89	87	85	85	85	84	83	83
9	96	90	87	84	95	90	86	84	89	86	84	84	88	86	84	84	88	85	83	83	83	82	81	81
10	94	88	85	83	93	88	85	82	87	84	82	82	87	84	82	82	86	84	82	82	82	81	80	80

**AVERAGE LUMINANCE (cd/sqm):**

0°	
0°	3090517
5°	2574984
10°	1510132
15°	528949
20°	178036
25°	68590
30°	31504
35°	13973
40°	6827
45°	3977
50°	2149
55°	688
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P492426

CATALOG NUMBER: LDA2B058050R20D010 2LBD1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	425.4	51.0
10°-20°	319.4	38.3
20°-30°	67.1	8.0
30°-40°	16.1	1.9
40°-50°	4.6	0.6
50°-60°	1.0	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	811.9	97.4
0°-40°	828.0	99.3
0°-60°	833.6	100.0
0°-90°	833.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	833.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6264	
5°	5199	425
15°	1036	319
25°	126	67
35°	23	16
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492426

CATALOG NUMBER: LDA2B058050R20D010 2LBD1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6264.2
1°	6187.8
2°	6000.8
3°	5785.3
4°	5544.2
5°	5199.4
6°	4833.5
7°	4427.3
8°	3963.4
9°	3495.0
10°	3014.4
11°	2520.0
12°	2084.6
13°	1659.7
14°	1321.0
15°	1035.6
16°	812.4
17°	640.8
18°	515.1
19°	417.6
20°	339.1
22.5°	205.7
25°	126.0
27.5°	82.5
30°	55.3
32.5°	33.7
35°	23.2
37.5°	15.9
40°	10.6
42.5°	7.7
45°	5.7
47.5°	4.1
50°	2.8
52.5°	1.6
55°	0.8
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P492426

CATALOG NUMBER: LDA2B058050R20D010 2LBD1B

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)