

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492435

Luminaire Tested: **LDA2B058050R20D010 2LBD1MMS-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492435
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058050R20D010 2LBD1MMS-30DEG TILT
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 530.3 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492435

CATALOG NUMBER: LDA2B058050R20D010 2LBD1MMS-30DEG TILT

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ····· 90°-270°



TEST NUMBER: P492435

CATALOG NUMBER: LDA2B058050R20D010 2LBD1MMS-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	8436	8436	8436
5°	16096	7429	5448
10°	38475	6513	3657
15°	224277	5210	1430
20°	1118775	3203	420
25°	2040006	1089	0
30°	2392678	0	0
35°	2094200	0	0
40°	1546529	0	0
45°	557408	0	0
50°	116051	0	0
55°	26579	344	0
60°	8387	395	0
65°	1868	934	0
70°	0	1154	577
75°	0	1525	0
80°	0	2273	0
85°	0	4529	0



TEST NUMBER: P492435

CATALOG NUMBER: LDA2B058050R20D010 2LBD1MMS-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1.9	0.4
10°-20°	29.1	5.5
20°-30°	196.4	37.0
30°-40°	229.4	43.3
40°-50°	66.9	12.6
50°-60°	4.5	0.8
60°-70°	0.8	0.2
70°-80°	0.7	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	227.4	42.9
0°-40°	456.9	86.2
0°-60°	528.3	99.6
0°-90°	530.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	530.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	17	17	17	17	17	
5°	32	24	15	13	11	4
15°	439	50	10	5	3	229
25°	3748	77	2	0	0	1659
35°	3477	42	0	0	0	2136
45°	799	8	0	0	0	736
55°	31	2	0	0	0	39
65°	2	1	1	1	0	3
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P492435

CATALOG NUMBER: LDA2B058050R20D010 2LBD1MMS-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1
2.5°	22.0	22.0	19.5	17.5	15.9	15.0	14.6	13.8	13.4
5°	32.5	28.5	23.6	18.3	15.0	13.8	12.6	11.4	11.0
7.5°	47.6	41.5	28.5	18.7	14.2	12.2	11.0	9.8	8.9
10°	76.8	59.8	35.0	18.7	13.0	10.6	8.9	7.7	7.3
12.5°	141.9	91.5	41.9	18.3	11.8	8.9	6.9	6.1	4.9
15°	439.1	189.5	49.6	17.5	10.2	6.9	5.3	3.3	2.8
17.5°	1135.6	442.4	55.3	15.5	8.1	4.9	2.4	2.0	2.0
20°	2130.9	802.2	63.4	13.4	6.1	3.3	1.6	1.2	0.8
21°	2431.0	981.5	67.5	12.6	5.3	2.0	1.2	0.4	0.4
22°	2897.3	1177.1	70.7	11.8	4.5	1.2	0.8	0.4	0.0
23°	3229.5	1301.9	74.0	10.6	3.3	1.2	0.4	0.0	0.0
24°	3561.7	1460.9	76.0	9.8	2.8	0.8	0.4	0.0	0.0
25°	3747.5	1593.4	76.8	8.9	2.0	0.4	0.0	0.0	0.0
26°	3900.4	1682.0	77.3	8.1	1.2	0.0	0.0	0.0	0.0
27°	4031.3	1784.9	76.4	7.3	1.2	0.0	0.0	0.0	0.0
28°	4105.7	1802.0	75.2	6.5	0.4	0.0	0.0	0.0	0.0
29°	4137.8	1781.2	71.6	5.7	0.4	0.0	0.0	0.0	0.0
30°	4200.0	1761.7	67.9	5.3	0.0	0.0	0.0	0.0	0.0
31°	4142.7	1697.1	63.4	4.5	0.0	0.0	0.0	0.0	0.0
32°	3918.2	1642.6	58.1	3.7	0.0	0.0	0.0	0.0	0.0
33°	3851.2	1530.8	52.4	3.3	0.0	0.0	0.0	0.0	0.0
34°	3724.7	1364.5	47.6	2.8	0.0	0.0	0.0	0.0	0.0
35°	3477.1	1227.1	41.5	2.4	0.0	0.0	0.0	0.0	0.0
36°	3304.3	1070.1	36.2	2.0	0.0	0.0	0.0	0.0	0.0
37°	3123.4	933.1	32.1	1.6	0.0	0.0	0.0	0.0	0.0
38°	2898.5	789.2	27.2	1.2	0.0	0.0	0.0	0.0	0.0
39°	2636.7	652.2	23.2	1.2	0.0	0.0	0.0	0.0	0.0
40°	2401.3	525.7	19.9	0.8	0.0	0.0	0.0	0.0	0.0
42.5°	1482.0	300.1	11.8	0.8	0.0	0.0	0.0	0.0	0.0
45°	798.9	182.1	8.5	0.4	0.0	0.0	0.0	0.0	0.0
47.5°	368.0	85.0	6.1	0.4	0.0	0.0	0.0	0.0	0.0
50°	151.2	37.8	4.5	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	54.5	21.1	2.8	0.0	0.0	0.4	0.0	0.0	0.0
55°	30.9	12.2	1.6	0.4	0.4	0.4	0.4	0.0	0.0
57.5°	14.6	6.9	0.4	0.4	0.4	0.4	0.4	0.0	0.0
60°	8.5	3.7	0.4	0.4	0.4	0.8	0.4	0.0	0.0
62.5°	4.1	1.2	0.4	0.8	0.8	0.8	0.8	0.4	0.0
65°	1.6	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.0
67.5°	0.4	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
70°	0.0	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
72.5°	0.0	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
75°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
77.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
80°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0



TEST NUMBER: P492435

CATALOG NUMBER: LDA2B058050R20D010 2LBD1MMS-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
85°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
87.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)