

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279948

Luminaire Tested: **LDA2B208050D010 EU2B20FL408050 2LBALD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208050D010 EU2B20FL408050 2LBALD1MW
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2257.7 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279948

CATALOG NUMBER: LDA2B208050D010 EU2B20FL408050 2LBALD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P279948

CATALOG NUMBER: LDA2B208050D010 EU2B20FL408050 2LBALD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																												
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																												
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																												
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																												
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																												
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																												
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																												
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																												
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																												
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3104430
5°	3038782
10°	2769628
15°	2163604
20°	1280955
25°	476210
30°	148802
35°	66191
40°	30721
45°	14443
50°	7982
55°	4473
60°	2072
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P279948

CATALOG NUMBER: LDA2B208050D010 EU2B20FL408050 2LBALD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	567.2	25.1
10°-20°	1127.9	50.0
20°-30°	461.9	20.5
30°-40°	76.5	3.4
40°-50°	18.1	0.8
50°-60°	4.8	0.2
60°-70°	1.1	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2157.0	95.5
0°-40°	2233.5	98.9
0°-60°	2256.4	99.9
0°-90°	2257.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2257.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6292	
5°	6136	567
15°	4236	1128
25°	875	462
35°	110	76
45°	21	18
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279948

CATALOG NUMBER: LDA2B208050D010 EU2B20FL408050 2LBALD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6292.4
1°	6270.6
2°	6241.6
3°	6215.7
4°	6181.5
5°	6135.9
6°	6068.5
7°	5980.4
8°	5855.0
9°	5702.6
10°	5528.5
11°	5326.4
12°	5098.4
13°	4838.2
14°	4549.0
15°	4236.0
17.5°	3359.2
20°	2439.8
22.5°	1561.9
25°	874.8
27.5°	461.2
30°	261.2
32.5°	165.8
35°	109.9
37.5°	72.6
40°	47.7
42.5°	31.1
45°	20.7
47.5°	14.5
50°	10.4
52.5°	7.3
55°	5.2
57.5°	3.1
60°	2.1
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279948

CATALOG NUMBER: LDA2B208050D010 EU2B20FL408050 2LBALD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)