

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280838

Luminaire Tested: **LDA2B208050D010 EU2B20WFL558050 2LBAD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280838
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208050D010 EU2B20WFL558050 2LBAD1WMH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2246.5 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280838

CATALOG NUMBER: LDA2B208050D010 EU2B20WFL558050 2LBAD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P280838

CATALOG NUMBER: LDA2B208050D010 EU2B20WFL558050 2LBAD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103		102	101	99		98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75		81	77	74		80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71		77	73	70		76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64		71	67	64		70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61		68	64	61		67	63	61	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1918635
5°	1879509
10°	1747844
15°	1526066
20°	1263472
25°	966356
30°	528782
35°	195742
40°	67753
45°	30560
50°	14430
55°	7139
60°	2072
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P280838

CATALOG NUMBER: LDA2B208050D010 EU2B20WFL558050 2LBAD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.7	15.7
10°-20°	825.8	36.8
20°-30°	780.5	34.7
30°-40°	240.3	10.7
40°-50°	38.0	1.7
50°-60°	8.0	0.4
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1959.0	87.2
0°-40°	2199.2	97.9
0°-60°	2245.3	99.9
0°-90°	2246.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2246.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3889	
5°	3795	353
15°	2988	826
25°	1775	781
35°	325	240
45°	44	38
55°	8	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280838

CATALOG NUMBER: LDA2B208050D010 EU2B20WFL558050 2LBAD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3888.9
1°	3874.3
2°	3856.6
3°	3842.0
4°	3823.3
5°	3795.1
6°	3758.7
7°	3709.7
8°	3644.1
9°	3568.0
10°	3488.9
11°	3401.3
12°	3308.6
13°	3207.6
14°	3102.4
15°	2987.8
17.5°	2684.6
20°	2406.5
22.5°	2124.2
25°	1775.2
27.5°	1354.3
30°	928.2
32.5°	569.8
35°	325.0
37.5°	181.3
40°	105.2
42.5°	65.6
45°	43.8
47.5°	29.2
50°	18.8
52.5°	12.5
55°	8.3
57.5°	5.2
60°	2.1
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280838

CATALOG NUMBER: LDA2B208050D010 EU2B20WFL558050 2LBAD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)