

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280183

Luminaire Tested: **LDA2B059024D010 EU2B05WFL559024 2LBAD1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280183
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059024D010 EU2B05WFL559024 2LBAD1WH
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, WH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 613.0 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280183

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBAD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P280183

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBAD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | |
| 1 | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 99 | 98 | 97 | 97 | 95 | | |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 98 | 95 | 97 | 95 | 93 | 95 | 93 | 91 | 90 | | |
| 3 | 105 | 99 | 95 | 91 | 103 | 98 | 94 | 91 | 95 | 92 | 89 | 93 | 90 | 88 | 91 | 88 | 86 | 85 | | |
| 4 | 100 | 94 | 89 | 85 | 99 | 93 | 88 | 85 | 91 | 87 | 84 | 89 | 85 | 83 | 87 | 84 | 82 | 80 | | |
| 5 | 96 | 89 | 84 | 80 | 95 | 88 | 83 | 80 | 86 | 82 | 79 | 85 | 81 | 78 | 83 | 80 | 78 | 76 | | |
| 6 | 92 | 84 | 79 | 75 | 91 | 84 | 79 | 75 | 82 | 78 | 75 | 81 | 77 | 74 | 80 | 76 | 74 | 72 | | |
| 7 | 88 | 80 | 75 | 71 | 87 | 80 | 75 | 71 | 78 | 74 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | 69 | | |
| 8 | 85 | 76 | 71 | 68 | 84 | 76 | 71 | 67 | 75 | 70 | 67 | 74 | 70 | 67 | 73 | 69 | 67 | 65 | | |
| 9 | 81 | 73 | 68 | 64 | 80 | 72 | 68 | 64 | 72 | 67 | 64 | 71 | 67 | 64 | 70 | 66 | 64 | 62 | | |
| 10 | 78 | 70 | 65 | 61 | 77 | 69 | 64 | 61 | 69 | 64 | 61 | 68 | 64 | 61 | 67 | 63 | 61 | 59 | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 523556 |
| 5° | 512877 |
| 10° | 476926 |
| 15° | 416427 |
| 20° | 344784 |
| 25° | 263690 |
| 30° | 144301 |
| 35° | 53423 |
| 40° | 18484 |
| 45° | 8303 |
| 50° | 3914 |
| 55° | 1978 |
| 60° | 592 |
| 65° | 350 |
| 70° | 433 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P280183

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBAD1WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 96.2 | 15.7 |
| 10°-20° | 225.3 | 36.8 |
| 20°-30° | 213.0 | 34.7 |
| 30°-40° | 65.6 | 10.7 |
| 40°-50° | 10.4 | 1.7 |
| 50°-60° | 2.2 | 0.4 |
| 60°-70° | 0.3 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 534.5 | 87.2 |
| 0°-40° | 600.1 | 97.9 |
| 0°-60° | 612.7 | 99.9 |
| 0°-90° | 613.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 613.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1061 | |
| 5° | 1036 | 96 |
| 15° | 815 | 225 |
| 25° | 484 | 213 |
| 35° | 89 | 66 |
| 45° | 12 | 10 |
| 55° | 2 | 2 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P280183

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBAD1WH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1061.2 |
| 1° | 1057.2 |
| 2° | 1052.4 |
| 3° | 1048.4 |
| 4° | 1043.3 |
| 5° | 1035.6 |
| 6° | 1025.6 |
| 7° | 1012.3 |
| 8° | 994.4 |
| 9° | 973.6 |
| 10° | 952.0 |
| 11° | 928.1 |
| 12° | 902.8 |
| 13° | 875.3 |
| 14° | 846.6 |
| 15° | 815.3 |
| 17.5° | 732.6 |
| 20° | 656.7 |
| 22.5° | 579.6 |
| 25° | 484.4 |
| 27.5° | 369.5 |
| 30° | 253.3 |
| 32.5° | 155.5 |
| 35° | 88.7 |
| 37.5° | 49.5 |
| 40° | 28.7 |
| 42.5° | 17.9 |
| 45° | 11.9 |
| 47.5° | 8.0 |
| 50° | 5.1 |
| 52.5° | 3.4 |
| 55° | 2.3 |
| 57.5° | 1.4 |
| 60° | 0.6 |
| 62.5° | 0.3 |
| 65° | 0.3 |
| 67.5° | 0.3 |
| 70° | 0.3 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P280183

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBAD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)