

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280850

Luminaire Tested: **LDA2B209024D010 EU2B20WFL559024 2LBAD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209024D010 EU2B20WFL559024 2LBAD1H
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1530.7 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280850

CATALOG NUMBER: LDA2B209024D010 EU2B20WFL559024 2LBAD1H

Luminous Intensity Polar Plot





TEST NUMBER: P280850

CATALOG NUMBER: LDA2B209024D010 EU2B20WFL559024 2LBAD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95	95	91	91	91	91	91	91	91	91	91	91	95																
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	91	91	91	91	91	91	91	91	91	91	91	91	90																
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85													85															
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80													80															
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76													76															
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72													72															
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69													69															
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65													65															
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62													62															
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59													59															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1307310
5°	1280658
10°	1190912
15°	1039817
20°	860883
25°	658409
30°	360326
35°	133406
40°	46178
45°	20792
50°	9824
55°	4903
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P280850

CATALOG NUMBER: LDA2B209024D010 EU2B20WFL559024 2LBAD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.3	15.7
10°-20°	562.7	36.8
20°-30°	531.8	34.7
30°-40°	163.7	10.7
40°-50°	25.9	1.7
50°-60°	5.5	0.4
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1334.8	87.2
0°-40°	1498.5	97.9
0°-60°	1529.8	99.9
0°-90°	1530.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1530.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2650	
5°	2586	240
15°	2036	563
25°	1210	532
35°	222	164
45°	30	26
55°	6	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280850

CATALOG NUMBER: LDA2B209024D010 EU2B20WFL559024 2LBAD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2649.8
1°	2639.9
2°	2627.8
3°	2617.8
4°	2605.1
5°	2585.9
6°	2561.1
7°	2527.7
8°	2483.0
9°	2431.2
10°	2377.2
11°	2317.6
12°	2254.4
13°	2185.6
14°	2113.9
15°	2035.8
17.5°	1829.2
20°	1639.7
22.5°	1447.3
25°	1209.5
27.5°	922.8
30°	632.5
32.5°	388.3
35°	221.5
37.5°	123.5
40°	71.7
42.5°	44.7
45°	29.8
47.5°	19.9
50°	12.8
52.5°	8.5
55°	5.7
57.5°	3.5
60°	1.4
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280850

CATALOG NUMBER: LDA2B209024D010 EU2B20WFL559024 2LBAD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)