

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280187

Luminaire Tested: **LDA2B059024D010 EU2B05WFL559024 2LBALD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059024D010 EU2B05WFL559024 2LBALD1H
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 600.5 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280187

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBALD1H

Luminous Intensity Polar Plot





TEST NUMBER: P280187

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBALD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	512899
5°	502427
10°	467257
15°	407949
20°	337748
25°	258301
30°	141339
35°	52338
40°	18097
45°	8163
50°	3838
55°	1892
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P280187

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBALD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	15.7
10°-20°	220.8	36.8
20°-30°	208.6	34.7
30°-40°	64.2	10.7
40°-50°	10.1	1.7
50°-60°	2.1	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	523.7	87.2
0°-40°	587.9	97.9
0°-60°	600.2	99.9
0°-90°	600.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	600.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1040	
5°	1014	94
15°	799	221
25°	474	209
35°	87	64
45°	12	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280187

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBALD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1039.6
1°	1035.7
2°	1031.0
3°	1027.1
4°	1022.0
5°	1014.5
6°	1004.8
7°	991.7
8°	974.1
9°	953.8
10°	932.7
11°	909.3
12°	884.5
13°	857.5
14°	829.3
15°	798.7
17.5°	717.7
20°	643.3
22.5°	567.8
25°	474.5
27.5°	362.0
30°	248.1
32.5°	152.3
35°	86.9
37.5°	48.5
40°	28.1
42.5°	17.5
45°	11.7
47.5°	7.8
50°	5.0
52.5°	3.3
55°	2.2
57.5°	1.4
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280187

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBALD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)