

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279129

Luminaire Tested: **LDA2B209040D010 EU2B20NFL259040 2LBAD1GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279129  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B209040D010 EU2B20NFL259040 2LBAD1GPH  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl, Self-Flanged, GPH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1793.9 lumens  
Efficiency: N/A  
Efficacy: 87.1 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279129

CATALOG NUMBER: LDA2B209040D010 EU2B20NFL259040 2LBAD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P279129

CATALOG NUMBER: LDA2B209040D010 EU2B20NFL259040 2LBAD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97				97															
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94				94															
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91				91															
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89				89															
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86				86															
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84				84															
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82				82															
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80				80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78				78															
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76				76															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4591866
5°	4234802
10°	2853741
15°	1407006
20°	600996
25°	236254
30°	93030
35°	40775
40°	19643
45°	9419
50°	5219
55°	2925
60°	1677
65°	934
70°	1154
75°	0
80°	0
85°	0



TEST NUMBER: P279129

CATALOG NUMBER: LDA2B209040D010 EU2B20NFL259040 2LBAD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	724.3	40.4
10°-20°	780.1	43.5
20°-30°	225.2	12.6
30°-40°	47.5	2.7
40°-50°	11.7	0.7
50°-60°	3.4	0.2
60°-70°	1.1	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1729.6	96.4
0°-40°	1777.2	99.1
0°-60°	1792.3	99.9
0°-90°	1793.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1793.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9307	
5°	8551	724
15°	2755	780
25°	434	225
35°	68	48
45°	14	12
55°	3	3
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P279129

CATALOG NUMBER: LDA2B209040D010 EU2B20NFL259040 2LBAD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9307.3
1°	9248.9
2°	9149.9
3°	9016.2
4°	8826.7
5°	8550.9
6°	8178.6
7°	7693.0
8°	7095.7
9°	6399.4
10°	5696.4
11°	4985.7
12°	4314.8
13°	3719.2
14°	3195.5
15°	2754.7
17.5°	1820.7
20°	1144.7
22.5°	703.9
25°	434.0
27.5°	264.8
30°	163.3
32.5°	103.2
35°	67.7
37.5°	44.8
40°	30.5
42.5°	21.2
45°	13.5
47.5°	8.5
50°	6.8
52.5°	5.1
55°	3.4
57.5°	2.5
60°	1.7
62.5°	1.7
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.8
80°	0.0
82.5°	0.0



TEST NUMBER: P279129

CATALOG NUMBER: LDA2B209040D010 EU2B20NFL259040 2LBAD1GPH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)