

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315180

Luminaire Tested: **LDA2B20NFL9040D010 PINW1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315180
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B20NFL9040D010 PINW1MMS
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in Adj PinHole, White oculus, matte metallic silver finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1570.7 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315180

CATALOG NUMBER: LDA2B20NFL9040D010 PINW1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P315180

CATALOG NUMBER: LDA2B20NFL9040D010 PINW1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4020405
5°	3707810
10°	2498601
15°	1231916
20°	526180
25°	206859
30°	81465
35°	35715
40°	17196
45°	8303
50°	4528
55°	2580
60°	1480
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P315180

CATALOG NUMBER: LDA2B20NFL9040D010 PINW1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	634.2	40.4
10°-20°	683.0	43.5
20°-30°	197.2	12.6
30°-40°	41.6	2.7
40°-50°	10.2	0.7
50°-60°	2.9	0.2
60°-70°	1.0	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1514.4	96.4
0°-40°	1556.1	99.1
0°-60°	1569.2	99.9
0°-90°	1570.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1570.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8149	
5°	7487	634
15°	2412	683
25°	380	197
35°	59	42
45°	12	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315180

CATALOG NUMBER: LDA2B20NFL9040D010 PINW1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	8149.0
1°	8097.9
2°	8011.2
3°	7894.2
4°	7728.3
5°	7486.8
6°	7160.9
7°	6735.7
8°	6212.7
9°	5603.1
10°	4987.5
11°	4365.3
12°	3777.8
13°	3256.3
14°	2797.8
15°	2411.9
17.5°	1594.1
20°	1002.2
22.5°	616.3
25°	380.0
27.5°	231.9
30°	143.0
32.5°	90.4
35°	59.3
37.5°	39.3
40°	26.7
42.5°	18.5
45°	11.9
47.5°	7.4
50°	5.9
52.5°	4.4
55°	3.0
57.5°	2.2
60°	1.5
62.5°	1.5
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.7
80°	0.0
82.5°	0.0



TEST NUMBER: P315180

CATALOG NUMBER: LDA2B20NFL9040D010 PINW1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)