

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492829

Luminaire Tested: **LDA2B059024R65D010 2LBDL1WHH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P492829  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059024R65D010 2LBDL1WHH  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 522.3 lumens  
Efficiency: N/A  
Efficacy: 74.6 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P492829

CATALOG NUMBER: LDA2B059024R65D010 2LBDL1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P492829

CATALOG NUMBER: LDA2B059024R65D010 2LBDL1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	95	90	86	100	94	89	86	91	88	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72		79	74	71		77	73	70	69
6	87	78	71	67	85	77	71	67	75	70	66		74	69	66		73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58		66	61	57		65	60	57	56
9	74	64	58	54	73	64	58	54	63	57	54		62	57	54		61	57	53	52
10	71	61	55	51	69	60	54	51	59	54	50		59	54	50		58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	273224
5°	261837
10°	249384
15°	236995
20°	220458
25°	203538
30°	176602
35°	126720
40°	68848
45°	29374
50°	12664
55°	4559
60°	789
65°	700
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P492829

CATALOG NUMBER: LDA2B059024R65D010 2LBDL1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.5	9.5
10°-20°	130.0	24.9
20°-30°	169.9	32.5
30°-40°	129.3	24.8
40°-50°	37.4	7.2
50°-60°	5.6	1.1
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	349.4	66.9
0°-40°	478.7	91.6
0°-60°	521.7	99.9
0°-90°	522.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	522.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	554	
5°	529	49
15°	464	130
25°	374	170
35°	210	129
45°	42	37
55°	5	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492829

CATALOG NUMBER: LDA2B059024R65D010 2LBDL1WHH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	553.8
1°	551.9
2°	548.8
3°	542.7
4°	536.0
5°	528.7
6°	521.8
7°	515.6
8°	509.8
9°	504.5
10°	497.8
11°	491.9
12°	485.8
13°	479.6
14°	472.9
15°	464.0
16°	457.3
17°	449.2
18°	436.9
19°	430.5
20°	419.9
21°	410.4
22.5°	395.9
23°	390.3
24°	381.7
25°	373.9
26°	363.6
27°	352.1
28°	339.6
29°	326.2
30°	310.0
32.5°	265.6
35°	210.4
37.5°	155.1
40°	106.9
42.5°	67.8
45°	42.1
47.5°	26.2
50°	16.5
52.5°	9.8
55°	5.3
57.5°	2.0
60°	0.8
62.5°	0.6
65°	0.6



TEST NUMBER: P492829

CATALOG NUMBER: LDA2B059024R65D010 2LBDL1WHH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)