

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280047

Luminaire Tested: **LDA2B209050D010 EU2B20FL409050 2LBALD1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280047
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209050D010 EU2B20FL409050 2LBALD1WH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, WH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1880.7 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280047

CATALOG NUMBER: LDA2B209050D010 EU2B20FL409050 2LBALD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P280047

CATALOG NUMBER: LDA2B209050D010 EU2B20FL409050 2LBALD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100																
	1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96	96	96	96	96	96	96	96	96	96	96	96																
	2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92	92	92	92	92	92	92	92	92	92	92	92																
	3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89																
	4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85	85	85	85	85	85	85	85	85	85	85	85																
	5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82	82	82	82	82	82	82	82	82	82	82	82																
	6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79	79	79	79	79	79	79	79	79	79	79	79																
	7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77	77	77	77	77	77	77	77	77	77	77	77																
	8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74	74	74	74	74	74	74	74	74	74	74	74																
	9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72	72	72	72	72	72	72	72	72	72	72	72																
	10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69	69	69	69	69	69	69	69	69	69	69	69																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2586054
5°	2531353
10°	2307130
15°	1802339
20°	1067060
25°	396678
30°	123963
35°	55109
40°	25568
45°	12071
50°	6601
55°	3699
60°	1677
65°	1051
70°	1298
75°	0
80°	0
85°	0



TEST NUMBER: P280047

CATALOG NUMBER: LDA2B209050D010 EU2B20FL409050 2LBALD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.5	25.1
10°-20°	939.6	50.0
20°-30°	384.8	20.5
30°-40°	63.7	3.4
40°-50°	15.1	0.8
50°-60°	4.0	0.2
60°-70°	1.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1796.8	95.5
0°-40°	1860.5	98.9
0°-60°	1879.6	99.9
0°-90°	1880.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1880.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5242	
5°	5111	472
15°	3529	940
25°	729	385
35°	92	64
45°	17	15
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280047

CATALOG NUMBER: LDA2B209050D010 EU2B20FL409050 2LBALD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5241.7
1°	5223.5
2°	5199.4
3°	5177.8
4°	5149.3
5°	5111.3
6°	5055.2
7°	4981.8
8°	4877.3
9°	4750.4
10°	4605.3
11°	4437.0
12°	4247.0
13°	4030.3
14°	3789.4
15°	3528.7
17.5°	2798.3
20°	2032.4
22.5°	1301.1
25°	728.7
27.5°	384.2
30°	217.6
32.5°	138.1
35°	91.5
37.5°	60.4
40°	39.7
42.5°	25.9
45°	17.3
47.5°	12.1
50°	8.6
52.5°	6.0
55°	4.3
57.5°	2.6
60°	1.7
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280047

CATALOG NUMBER: LDA2B209050D010 EU2B20FL409050 2LBALD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)