

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279142

Luminaire Tested: **LDA2B209050D010 EU2B20NFL259050 2LBAD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279142  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B209050D010 EU2B20NFL259050 2LBAD1WMH  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl, Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1843.1 lumens  
Efficiency: N/A  
Efficacy: 89.5 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279142

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBAD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P279142

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBAD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 115 | 113 | 111 | 110 | 113 | 111 | 109 | 108 | 107 | 106 | 105 | 103 | 102 | 102 | 100 | 99  | 99  | 97  | 97  | 97  | 97  |
| 2   | 112 | 108 | 105 | 103 | 110 | 107 | 104 | 102 | 103 | 101 | 100 | 101 | 99  | 98  | 98  | 97  | 96  | 94  | 94  | 94  | 94  |
| 3   | 108 | 104 | 100 | 98  | 107 | 103 | 99  | 97  | 100 | 98  | 95  | 98  | 96  | 94  | 96  | 94  | 93  | 91  | 91  | 91  | 91  |
| 4   | 105 | 100 | 96  | 94  | 104 | 99  | 96  | 93  | 97  | 94  | 92  | 95  | 93  | 91  | 94  | 92  | 90  | 89  | 89  | 89  | 89  |
| 5   | 102 | 97  | 93  | 90  | 101 | 96  | 92  | 90  | 94  | 91  | 89  | 93  | 90  | 88  | 92  | 89  | 87  | 86  | 86  | 86  | 86  |
| 6   | 100 | 94  | 90  | 87  | 98  | 93  | 89  | 87  | 92  | 89  | 86  | 91  | 88  | 86  | 89  | 87  | 85  | 84  | 84  | 84  | 84  |
| 7   | 97  | 91  | 87  | 84  | 96  | 90  | 87  | 84  | 89  | 86  | 84  | 88  | 85  | 83  | 87  | 85  | 83  | 82  | 82  | 82  | 82  |
| 8   | 95  | 88  | 85  | 82  | 94  | 88  | 84  | 82  | 87  | 84  | 81  | 86  | 83  | 81  | 85  | 83  | 81  | 80  | 80  | 80  | 80  |
| 9   | 92  | 86  | 82  | 80  | 92  | 86  | 82  | 80  | 85  | 82  | 79  | 84  | 81  | 79  | 84  | 81  | 79  | 78  | 78  | 78  | 78  |
| 10  | 90  | 84  | 80  | 78  | 90  | 84  | 80  | 78  | 83  | 80  | 77  | 82  | 79  | 77  | 82  | 79  | 77  | 76  | 76  | 76  | 76  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 4717476 |
| 5°  | 4350640 |
| 10° | 2931792 |
| 15° | 1445518 |
| 20° | 617429  |
| 25° | 242732  |
| 30° | 95593   |
| 35° | 41859   |
| 40° | 20158   |
| 45° | 9698    |
| 50° | 5373    |
| 55° | 3011    |
| 60° | 1677    |
| 65° | 1051    |
| 70° | 1298    |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P279142

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBAD1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 744.1  | 40.4      |
| 10°-20°   | 801.4  | 43.5      |
| 20°-30°   | 231.4  | 12.6      |
| 30°-40°   | 48.8   | 2.7       |
| 40°-50°   | 12.0   | 0.7       |
| 50°-60°   | 3.5    | 0.2       |
| 60°-70°   | 1.2    | 0.1       |
| 70°-80°   | 0.6    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1777.0 | 96.4      |
| 0°-40°    | 1825.8 | 99.1      |
| 0°-60°    | 1841.3 | 99.9      |
| 0°-90°    | 1843.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1843.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 9562 |      |
| 5°  | 8785 | 744  |
| 15° | 2830 | 801  |
| 25° | 446  | 231  |
| 35° | 70   | 49   |
| 45° | 14   | 12   |
| 55° | 4    | 3    |
| 65° | 1    | 1    |
| 75° | 0    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P279142

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBAD1WMH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 9561.9 |
| 1°    | 9501.9 |
| 2°    | 9400.2 |
| 3°    | 9262.9 |
| 4°    | 9068.2 |
| 5°    | 8784.8 |
| 6°    | 8402.4 |
| 7°    | 7903.5 |
| 8°    | 7289.8 |
| 9°    | 6574.5 |
| 10°   | 5852.2 |
| 11°   | 5122.1 |
| 12°   | 4432.8 |
| 13°   | 3820.9 |
| 14°   | 3282.9 |
| 15°   | 2830.1 |
| 17.5° | 1870.5 |
| 20°   | 1176.0 |
| 22.5° | 723.2  |
| 25°   | 445.9  |
| 27.5° | 272.1  |
| 30°   | 167.8  |
| 32.5° | 106.0  |
| 35°   | 69.5   |
| 37.5° | 46.1   |
| 40°   | 31.3   |
| 42.5° | 21.7   |
| 45°   | 13.9   |
| 47.5° | 8.7    |
| 50°   | 7.0    |
| 52.5° | 5.2    |
| 55°   | 3.5    |
| 57.5° | 2.6    |
| 60°   | 1.7    |
| 62.5° | 1.7    |
| 65°   | 0.9    |
| 67.5° | 0.9    |
| 70°   | 0.9    |
| 72.5° | 0.9    |
| 75°   | 0.0    |
| 77.5° | 0.9    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P279142

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBAD1WMH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)