

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280930

Luminaire Tested: **LDA2B209050D010 EU2B20WFL559050 2LBAD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209050D010 EU2B20WFL559050 2LBAD1H
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1874.3 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280930

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBAD1H

Luminous Intensity Polar Plot





TEST NUMBER: P280930

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBAD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1600762
5°	1568148
10°	1458231
15°	1273237
20°	1054144
25°	806258
30°	441164
35°	163339
40°	56547
45°	25467
50°	11974
55°	6021
60°	1677
65°	1051
70°	1298
75°	0
80°	0
85°	0



TEST NUMBER: P280930

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBAD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.2	15.7
10°-20°	689.0	36.8
20°-30°	651.2	34.7
30°-40°	200.5	10.7
40°-50°	31.7	1.7
50°-60°	6.7	0.4
60°-70°	1.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1634.4	87.2
0°-40°	1834.9	97.9
0°-60°	1873.2	99.9
0°-90°	1874.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1874.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3245	
5°	3166	294
15°	2493	689
25°	1481	651
35°	271	200
45°	36	32
55°	7	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280930

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBAD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3244.6
1°	3232.4
2°	3217.6
3°	3205.5
4°	3189.8
5°	3166.4
6°	3135.9
7°	3095.1
8°	3040.3
9°	2976.9
10°	2910.8
11°	2837.8
12°	2760.5
13°	2676.1
14°	2588.4
15°	2492.8
17.5°	2239.8
20°	2007.8
22.5°	1772.2
25°	1481.1
27.5°	1129.9
30°	774.4
32.5°	475.4
35°	271.2
37.5°	151.2
40°	87.8
42.5°	54.8
45°	36.5
47.5°	24.3
50°	15.6
52.5°	10.4
55°	7.0
57.5°	4.3
60°	1.7
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280930

CATALOG NUMBER: LDA2B209050D010 EU2B20WFL559050 2LBAD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)