

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P493025

Luminaire Tested: **LDA2B059027R60D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P493025
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B059027R60D010 2LBDLC1MMS
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 593.4 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P493025

CATALOG NUMBER: LDA2B059027R60D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P493025

CATALOG NUMBER: LDA2B059027R60D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	351175
5°	342017
10°	332596
15°	316113
20°	288816
25°	248012
30°	184578
35°	108351
40°	51652
45°	24071
50°	11974
55°	4215
60°	987
65°	817
70°	433
75°	572
80°	0
85°	0



TEST NUMBER: P493025

CATALOG NUMBER: LDA2B059027R60D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	11.0
10°-20°	172.2	29.0
20°-30°	204.5	34.5
30°-40°	115.4	19.5
40°-50°	30.0	5.1
50°-60°	5.5	0.9
60°-70°	0.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.7	74.4
0°-40°	557.1	93.9
0°-60°	592.6	99.9
0°-90°	593.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	593.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	712	
5°	691	65
15°	619	172
25°	456	204
35°	180	115
45°	34	30
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P493025

CATALOG NUMBER: LDA2B059027R60D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	711.8
1°	712.1
2°	707.2
3°	703.0
4°	694.8
5°	690.6
6°	683.1
7°	677.6
8°	672.4
9°	668.8
10°	663.9
11°	654.4
12°	645.6
13°	640.7
14°	629.3
15°	618.9
16°	606.9
17°	592.5
18°	578.8
19°	562.5
20°	550.1
21°	533.2
22.5°	505.2
23°	500.3
24°	476.5
25°	455.6
26°	432.5
27°	405.8
28°	379.4
29°	353.6
30°	324.0
32.5°	249.3
35°	179.9
37.5°	122.9
40°	80.2
42.5°	52.5
45°	34.5
47.5°	23.5
50°	15.6
52.5°	9.8
55°	4.9
57.5°	2.0
60°	1.0
62.5°	0.7
65°	0.7



TEST NUMBER: P493025

CATALOG NUMBER: LDA2B059027R60D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)