

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279347

Luminaire Tested: **LDA2B059040D010 EU2B05FL409040 2LBAD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059040D010 EU2B05FL409040 2LBAD1LI
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 738.5 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279347

CATALOG NUMBER: LDA2B059040D010 EU2B05FL409040 2LBAD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P279347

CATALOG NUMBER: LDA2B059040D010 EU2B05FL409040 2LBAD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89		
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85		
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82		
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79		
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	73	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1015487
5°	994009
10°	906009
15°	707768
20°	419022
25°	155797
30°	48651
35°	21622
40°	10047
45°	4744
50°	2610
55°	1462
60°	691
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P279347

CATALOG NUMBER: LDA2B059040D010 EU2B05FL409040 2LBAD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.5	25.1
10°-20°	369.0	50.0
20°-30°	151.1	20.5
30°-40°	25.0	3.4
40°-50°	5.9	0.8
50°-60°	1.6	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	705.6	95.5
0°-40°	730.6	98.9
0°-60°	738.1	99.9
0°-90°	738.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	738.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2058	
5°	2007	186
15°	1386	369
25°	286	151
35°	36	25
45°	7	6
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279347

CATALOG NUMBER: LDA2B059040D010 EU2B05FL409040 2LBAD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2058.3
1°	2051.2
2°	2041.7
3°	2033.2
4°	2022.1
5°	2007.1
6°	1985.1
7°	1956.3
8°	1915.3
9°	1865.4
10°	1808.5
11°	1742.3
12°	1667.8
13°	1582.7
14°	1488.1
15°	1385.7
17.5°	1098.8
20°	798.1
22.5°	510.9
25°	286.2
27.5°	150.9
30°	85.4
32.5°	54.2
35°	35.9
37.5°	23.7
40°	15.6
42.5°	10.2
45°	6.8
47.5°	4.7
50°	3.4
52.5°	2.4
55°	1.7
57.5°	1.0
60°	0.7
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279347

CATALOG NUMBER: LDA2B059040D010 EU2B05FL409040 2LBAD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)