

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278463

Luminaire Tested: **LDA2B059040D010 EU2B05NFL259040 2LBALD1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059040D010 EU2B05NFL259040 2LBALD1WH
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, WH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 665.3 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278463

CATALOG NUMBER: LDA2B059040D010 EU2B05NFL259040 2LBALD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P278463

CATALOG NUMBER: LDA2B059040D010 EU2B05NFL259040 2LBALD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1703085
5°	1570624
10°	1058405
15°	521849
20°	222925
25°	87643
30°	34523
35°	15117
40°	7278
45°	3489
50°	1919
55°	1118
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P278463

CATALOG NUMBER: LDA2B059040D010 EU2B05NFL259040 2LBALD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.6	40.4
10°-20°	289.3	43.5
20°-30°	83.5	12.6
30°-40°	17.6	2.7
40°-50°	4.3	0.6
50°-60°	1.3	0.2
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	641.5	96.4
0°-40°	659.2	99.1
0°-60°	664.7	99.9
0°-90°	665.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	665.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3452	
5°	3171	269
15°	1022	289
25°	161	84
35°	25	18
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278463

CATALOG NUMBER: LDA2B059040D010 EU2B05NFL259040 2LBALD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3452.0
1°	3430.3
2°	3393.6
3°	3344.0
4°	3273.7
5°	3171.4
6°	3033.4
7°	2853.3
8°	2631.7
9°	2373.5
10°	2112.7
11°	1849.1
12°	1600.3
13°	1379.4
14°	1185.2
15°	1021.7
17.5°	675.3
20°	424.6
22.5°	261.1
25°	161.0
27.5°	98.2
30°	60.6
32.5°	38.3
35°	25.1
37.5°	16.6
40°	11.3
42.5°	7.8
45°	5.0
47.5°	3.1
50°	2.5
52.5°	1.9
55°	1.3
57.5°	0.9
60°	0.6
62.5°	0.6
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.3
80°	0.0
82.5°	0.0



TEST NUMBER: P278463

CATALOG NUMBER: LDA2B059040D010 EU2B05NFL259040 2LBALD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)