

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P493274

Luminaire Tested: **LDA2B059030R70D010 2LBD1WHH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P493274  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059030R70D010 2LBD1WHH  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 615.0 lumens  
Efficiency: N/A  
Efficacy: 87.9 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P493274

CATALOG NUMBER: LDA2B059030R70D010 2LBD1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P493274

CATALOG NUMBER: LDA2B059030R70D010 2LBD1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58		67	62	58		66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54		62	57	54		61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50		59	54	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	240317
5°	237669
10°	236459
15°	235667
20°	227231
25°	217855
30°	215683
35°	184178
40°	114961
45°	53166
50°	19265
55°	1376
60°	592
65°	700
70°	433
75°	572
80°	0
85°	0



TEST NUMBER: P493274

CATALOG NUMBER: LDA2B059030R70D010 2LBD1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.5	7.4
10°-20°	129.2	21.0
20°-30°	185.8	30.2
30°-40°	183.2	29.8
40°-50°	65.3	10.6
50°-60°	5.4	0.9
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.6	58.6
0°-40°	543.7	88.4
0°-60°	614.3	99.9
0°-90°	615.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	615.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	487	
5°	480	46
15°	461	129
25°	400	186
35°	306	183
45°	76	65
55°	2	5
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P493274

CATALOG NUMBER: LDA2B059030R70D010 2LBD1WHH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	487.1
1°	487.1
2°	486.2
3°	486.5
4°	482.4
5°	479.9
6°	476.4
7°	475.2
8°	473.6
9°	473.3
10°	472.0
11°	470.5
12°	470.5
13°	467.7
14°	463.9
15°	461.4
16°	456.4
17°	453.5
18°	444.8
19°	438.8
20°	432.8
21°	425.0
22.5°	414.0
23°	409.6
24°	405.6
25°	400.2
26°	397.1
27°	391.8
28°	391.1
29°	385.5
30°	378.6
32.5°	351.9
35°	305.8
37.5°	245.9
40°	178.5
42.5°	122.0
45°	76.2
47.5°	45.5
50°	25.1
52.5°	9.4
55°	1.6
57.5°	0.9
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P493274

CATALOG NUMBER: LDA2B059030R70D010 2LBD1WHH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)