

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279364

Luminaire Tested: **LDA2B059050D010 EU2B05FL409050 2LBAD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279364
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059050D010 EU2B05FL409050 2LBAD1MW
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 752.1 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279364

CATALOG NUMBER: LDA2B059050D010 EU2B05FL409050 2LBAD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P279364

CATALOG NUMBER: LDA2B059050D010 EU2B05FL409050 2LBAD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89		
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85		
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82		
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79		
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	73	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1034284
5°	1012383
10°	922742
15°	720844
20°	426793
25°	158628
30°	49563
35°	22044
40°	10240
45°	4814
50°	2686
55°	1462
60°	691
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P279364

CATALOG NUMBER: LDA2B059050D010 EU2B05FL409050 2LBAD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	25.1
10°-20°	375.8	50.0
20°-30°	153.9	20.5
30°-40°	25.5	3.4
40°-50°	6.0	0.8
50°-60°	1.6	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	718.6	95.5
0°-40°	744.1	98.9
0°-60°	751.7	99.9
0°-90°	752.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	752.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2096	
5°	2044	189
15°	1411	376
25°	291	154
35°	37	25
45°	7	6
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279364

CATALOG NUMBER: LDA2B059050D010 EU2B05FL409050 2LBAD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2096.4
1°	2089.1
2°	2079.4
3°	2070.8
4°	2059.4
5°	2044.2
6°	2021.8
7°	1992.4
8°	1950.6
9°	1899.9
10°	1841.9
11°	1774.5
12°	1698.6
13°	1611.9
14°	1515.6
15°	1411.3
17.5°	1119.1
20°	812.9
22.5°	520.4
25°	291.4
27.5°	153.7
30°	87.0
32.5°	55.2
35°	36.6
37.5°	24.2
40°	15.9
42.5°	10.4
45°	6.9
47.5°	4.8
50°	3.5
52.5°	2.4
55°	1.7
57.5°	1.0
60°	0.7
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279364

CATALOG NUMBER: LDA2B059050D010 EU2B05FL409050 2LBAD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)