

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279303

Luminaire Tested: **LDA2B059027D010 EU2B05FL409027 2LBAD1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279303  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B059027D010 EU2B05FL409027 2LBAD1WH  
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl, Self-Flanged, WH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 661.9 lumens  
Efficiency: N/A  
Efficacy: 94.6 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279303

CATALOG NUMBER: LDA2B059027D010 EU2B05FL409027 2LBAD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P279303

CATALOG NUMBER: LDA2B059027D010 EU2B05FL409027 2LBAD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89		
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85		
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82		
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79		
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	910104
5°	890849
10°	811977
15°	634320
20°	375550
25°	139629
30°	43638
35°	19394
40°	9017
45°	4256
50°	2303
55°	1290
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P279303

CATALOG NUMBER: LDA2B059027D010 EU2B05FL409027 2LBAD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.3	25.1
10°-20°	330.7	50.0
20°-30°	135.4	20.5
30°-40°	22.4	3.4
40°-50°	5.3	0.8
50°-60°	1.4	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	632.4	95.5
0°-40°	654.8	98.9
0°-60°	661.5	99.9
0°-90°	661.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	661.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1845	
5°	1799	166
15°	1242	331
25°	256	135
35°	32	22
45°	6	5
55°	2	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279303

CATALOG NUMBER: LDA2B059027D010 EU2B05FL409027 2LBAD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1844.7
1°	1838.4
2°	1829.8
3°	1822.2
4°	1812.2
5°	1798.8
6°	1779.1
7°	1753.3
8°	1716.5
9°	1671.8
10°	1620.8
11°	1561.5
12°	1494.7
13°	1418.4
14°	1333.6
15°	1241.9
17.5°	984.8
20°	715.3
22.5°	457.9
25°	256.5
27.5°	135.2
30°	76.6
32.5°	48.6
35°	32.2
37.5°	21.3
40°	14.0
42.5°	9.1
45°	6.1
47.5°	4.3
50°	3.0
52.5°	2.1
55°	1.5
57.5°	0.9
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279303

CATALOG NUMBER: LDA2B059027D010 EU2B05FL409027 2LBAD1WH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)