

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279310

Luminaire Tested: **LDA2B059027D010 EU2B05FL409027 2LBALD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279310  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B059027D010 EU2B05FL409027 2LBALD1WMH  
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 649.2 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279310

CATALOG NUMBER: LDA2B059027D010 EU2B05FL409027 2LBALD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P279310

CATALOG NUMBER: LDA2B059027D010 EU2B05FL409027 2LBALD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	892590
5°	873714
10°	796346
15°	622113
20°	368305
25°	136908
30°	42783
35°	19032
40°	8823
45°	4186
50°	2303
55°	1290
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P279310

CATALOG NUMBER: LDA2B059027D010 EU2B05FL409027 2LBALD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.1	25.1
10°-20°	324.3	50.0
20°-30°	132.8	20.5
30°-40°	22.0	3.4
40°-50°	5.2	0.8
50°-60°	1.4	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	620.2	95.5
0°-40°	642.2	98.9
0°-60°	648.8	99.9
0°-90°	649.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	649.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1809	
5°	1764	163
15°	1218	324
25°	252	133
35°	32	22
45°	6	5
55°	2	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279310

CATALOG NUMBER: LDA2B059027D010 EU2B05FL409027 2LBALD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1809.2
1°	1802.9
2°	1794.6
3°	1787.1
4°	1777.3
5°	1764.2
6°	1744.8
7°	1719.5
8°	1683.4
9°	1639.6
10°	1589.6
11°	1531.5
12°	1465.9
13°	1391.1
14°	1308.0
15°	1218.0
17.5°	965.8
20°	701.5
22.5°	449.1
25°	251.5
27.5°	132.6
30°	75.1
32.5°	47.7
35°	31.6
37.5°	20.9
40°	13.7
42.5°	8.9
45°	6.0
47.5°	4.2
50°	3.0
52.5°	2.1
55°	1.5
57.5°	0.9
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279310

CATALOG NUMBER: LDA2B059027D010 EU2B05FL409027 2LBALD1WMH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)