

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P277907

Luminaire Tested: **LDA2B059027D010 EU2B05SP159027 2LBAD1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P277907  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B059027D010 EU2B05SP159027 2LBAD1LI  
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in  
ADJ spun Refl, Self-Flanged, LI  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 615.7 lumens  
Efficiency: N/A  
Efficacy: 88.0 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P277907

CATALOG NUMBER: LDA2B059027D010 EU2B05SP159027 2LBAD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P277907

CATALOG NUMBER: LDA2B059027D010 EU2B05SP159027 2LBAD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	98	98	98
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96	96	96	96
3	110	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93	93	93	93
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92	92	92	92
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90	90	90	90
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88	88	88	88
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86	86	86	86
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85	85	85	85
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83	83	83	83
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82	82	82	82

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2781475
5°	2217565
10°	962769
15°	332611
20°	136401
25°	61622
30°	24781
35°	11564
40°	6247
45°	2302
50°	1382
55°	1032
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P277907

CATALOG NUMBER: LDA2B059027D010 EU2B05SP159027 2LBAD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	338.4	55.0
10°-20°	203.2	33.0
20°-30°	55.9	9.1
30°-40°	13.3	2.2
40°-50°	3.3	0.5
50°-60°	1.1	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	597.6	97.1
0°-40°	610.9	99.2
0°-60°	615.2	99.9
0°-90°	615.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	615.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5638	
5°	4478	338
15°	651	203
25°	113	56
35°	19	13
45°	3	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P277907

CATALOG NUMBER: LDA2B059027D010 EU2B05SP159027 2LBAD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5637.8
1°	5575.5
2°	5426.1
3°	5198.3
4°	4876.8
5°	4477.7
6°	3990.4
7°	3456.6
8°	2895.7
9°	2379.8
10°	1921.8
11°	1533.9
12°	1220.9
13°	984.6
14°	796.6
15°	651.2
17.5°	404.2
20°	259.8
22.5°	170.3
25°	113.2
27.5°	72.7
30°	43.5
32.5°	27.4
35°	19.2
37.5°	14.0
40°	9.7
42.5°	5.8
45°	3.3
47.5°	2.4
50°	1.8
52.5°	1.5
55°	1.2
57.5°	0.9
60°	0.6
62.5°	0.6
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P277907

CATALOG NUMBER: LDA2B059027D010 EU2B05SP159027 2LBAD1LI

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)