

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279156

Luminaire Tested: **LDA2B209727D010 EU2B20NFL259727 2LBAD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279156
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209727D010 EU2B20NFL259727 2LBAD1MW
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl, Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1459.3 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279156

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBAD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P279156

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBAD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3735193
5°	3444736
10°	2321307
15°	1144524
20°	488850
25°	192161
30°	75654
35°	33186
40°	15972
45°	7675
50°	4221
55°	2408
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P279156

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBAD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	589.2	40.4
10°-20°	634.5	43.5
20°-30°	183.2	12.6
30°-40°	38.7	2.7
40°-50°	9.5	0.7
50°-60°	2.8	0.2
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1406.9	96.4
0°-40°	1445.6	99.1
0°-60°	1457.9	99.9
0°-90°	1459.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1459.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7571	
5°	6956	589
15°	2241	635
25°	353	183
35°	55	39
45°	11	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279156

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBAD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7570.9
1°	7523.4
2°	7442.9
3°	7334.1
4°	7180.0
5°	6955.6
6°	6652.8
7°	6257.8
8°	5771.9
9°	5205.5
10°	4633.6
11°	4055.6
12°	3509.8
13°	3025.3
14°	2599.3
15°	2240.8
17.5°	1481.0
20°	931.1
22.5°	572.6
25°	353.0
27.5°	215.4
30°	132.8
32.5°	84.0
35°	55.1
37.5°	36.5
40°	24.8
42.5°	17.2
45°	11.0
47.5°	6.9
50°	5.5
52.5°	4.1
55°	2.8
57.5°	2.1
60°	1.4
62.5°	1.4
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.7
80°	0.0
82.5°	0.0



TEST NUMBER: P279156

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBAD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)