

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279169

Luminaire Tested: **LDA2B209727D010 EU2B20NFL259727 2LBALD1GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279169  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B209727D010 EU2B20NFL259727 2LBALD1GPH  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl w/lens Self-Flanged, GPH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1361.1 lumens  
Efficiency: N/A  
Efficacy: 66.1 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279169

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBALD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P279169

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBALD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3483973
5°	3213059
10°	2165204
15°	1067551
20°	455984
25°	179259
30°	70584
35°	30957
40°	14877
45°	7187
50°	3914
55°	2236
60°	1283
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P279169

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBALD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	549.6	40.4
10°-20°	591.9	43.5
20°-30°	170.9	12.6
30°-40°	36.1	2.7
40°-50°	8.9	0.7
50°-60°	2.6	0.2
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1312.3	96.4
0°-40°	1348.4	99.1
0°-60°	1359.8	99.9
0°-90°	1361.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1361.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7062	
5°	6488	550
15°	2090	592
25°	329	171
35°	51	36
45°	10	9
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279169

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBALD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7061.7
1°	7017.4
2°	6942.3
3°	6840.9
4°	6697.1
5°	6487.8
6°	6205.4
7°	5836.9
8°	5383.8
9°	4855.5
10°	4322.0
11°	3782.8
12°	3273.8
13°	2821.9
14°	2424.5
15°	2090.1
17.5°	1381.4
20°	868.5
22.5°	534.1
25°	329.3
27.5°	200.9
30°	123.9
32.5°	78.3
35°	51.4
37.5°	34.0
40°	23.1
42.5°	16.0
45°	10.3
47.5°	6.4
50°	5.1
52.5°	3.9
55°	2.6
57.5°	1.9
60°	1.3
62.5°	1.3
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.6
80°	0.0
82.5°	0.0



TEST NUMBER: P279169

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBALD1GPH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)