

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279166

Luminaire Tested: **LDA2B209727D010 EU2B20NFL259727 2LBALD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279166
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209727D010 EU2B20NFL259727 2LBALD1WMH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in ADJ spun Refl w/lens Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1361.1 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279166

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBALD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P279166

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBALD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97				97															
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94				94															
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91				91															
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89				89															
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86				86															
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84				84															
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82				82															
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80				80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78				78															
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76				76															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3483973
5°	3213059
10°	2165204
15°	1067551
20°	455984
25°	179259
30°	70584
35°	30957
40°	14877
45°	7187
50°	3914
55°	2236
60°	1283
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P279166

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBALD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	549.6	40.4
10°-20°	591.9	43.5
20°-30°	170.9	12.6
30°-40°	36.1	2.7
40°-50°	8.9	0.7
50°-60°	2.6	0.2
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1312.3	96.4
0°-40°	1348.4	99.1
0°-60°	1359.8	99.9
0°-90°	1361.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1361.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7062	
5°	6488	550
15°	2090	592
25°	329	171
35°	51	36
45°	10	9
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279166

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBALD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7061.7
1°	7017.4
2°	6942.3
3°	6840.9
4°	6697.1
5°	6487.8
6°	6205.4
7°	5836.9
8°	5383.8
9°	4855.5
10°	4322.0
11°	3782.8
12°	3273.8
13°	2821.9
14°	2424.5
15°	2090.1
17.5°	1381.4
20°	868.5
22.5°	534.1
25°	329.3
27.5°	200.9
30°	123.9
32.5°	78.3
35°	51.4
37.5°	34.0
40°	23.1
42.5°	16.0
45°	10.3
47.5°	6.4
50°	5.1
52.5°	3.9
55°	2.6
57.5°	1.9
60°	1.3
62.5°	1.3
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.6
80°	0.0
82.5°	0.0



TEST NUMBER: P279166

CATALOG NUMBER: LDA2B209727D010 EU2B20NFL259727 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)