

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279318

Luminaire Tested: **LDA2B059030D010 EU2B05FL409030 2LBAD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279318  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B059030D010 EU2B05FL409030 2LBAD1WMH  
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl, Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 690.5 lumens  
Efficiency: N/A  
Efficacy: 98.6 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279318

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBAD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P279318

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBAD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93		96	94	92		94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89		93	90	88		91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85		90	87	84		88	86	83	82
6	97	90	85	82	95	89	85	82	88	84	82		87	83	81		85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78		84	81	78		83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73		79	75	73		78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71		76	73	70		76	72	70	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	949524
5°	929429
10°	847145
15°	661748
20°	391826
25°	145672
30°	45518
35°	20237
40°	9403
45°	4396
50°	2456
55°	1376
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P279318

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBAD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	173.5	25.1
10°-20°	345.0	50.0
20°-30°	141.3	20.5
30°-40°	23.4	3.4
40°-50°	5.5	0.8
50°-60°	1.5	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	659.8	95.5
0°-40°	683.1	98.9
0°-60°	690.1	99.9
0°-90°	690.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	690.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1925	
5°	1877	173
15°	1296	345
25°	268	141
35°	34	23
45°	6	6
55°	2	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279318

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBAD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1924.6
1°	1917.9
2°	1909.1
3°	1901.1
4°	1890.7
5°	1876.7
6°	1856.1
7°	1829.2
8°	1790.8
9°	1744.2
10°	1691.0
11°	1629.1
12°	1559.4
13°	1479.8
14°	1391.4
15°	1295.6
17.5°	1027.4
20°	746.3
22.5°	477.7
25°	267.6
27.5°	141.1
30°	79.9
32.5°	50.7
35°	33.6
37.5°	22.2
40°	14.6
42.5°	9.5
45°	6.3
47.5°	4.4
50°	3.2
52.5°	2.2
55°	1.6
57.5°	1.0
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279318

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBAD1WMH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)