

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279327

Luminaire Tested: **LDA2B059030D010 EU2B05FL409030 2LBALD1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279327  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B059030D010 EU2B05FL409030 2LBALD1WH  
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, WH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 686.5 lumens  
Efficiency: N/A  
Efficacy: 98.1 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279327

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBALD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P279327

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBALD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	944048
5°	924080
10°	842235
15°	657968
20°	389516
25°	144801
30°	45233
35°	20116
40°	9339
45°	4396
50°	2456
55°	1376
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P279327

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBALD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.5	25.1
10°-20°	343.0	50.0
20°-30°	140.5	20.5
30°-40°	23.2	3.4
40°-50°	5.5	0.8
50°-60°	1.5	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	655.9	95.5
0°-40°	679.2	98.9
0°-60°	686.2	99.9
0°-90°	686.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	686.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1914	
5°	1866	172
15°	1288	343
25°	266	140
35°	33	23
45°	6	6
55°	2	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279327

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBALD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1913.5
1°	1906.9
2°	1898.0
3°	1890.2
4°	1879.8
5°	1865.9
6°	1845.4
7°	1818.6
8°	1780.5
9°	1734.1
10°	1681.2
11°	1619.7
12°	1550.4
13°	1471.3
14°	1383.3
15°	1288.2
17.5°	1021.5
20°	741.9
22.5°	475.0
25°	266.0
27.5°	140.3
30°	79.4
32.5°	50.4
35°	33.4
37.5°	22.1
40°	14.5
42.5°	9.5
45°	6.3
47.5°	4.4
50°	3.2
52.5°	2.2
55°	1.6
57.5°	0.9
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279327

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBALD1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)