

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280963

Luminaire Tested: **LDA2B209730D010 EU2B20WFL559730 2LBAD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209730D010 EU2B20WFL559730 2LBAD1LI
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1589.1 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280963

CATALOG NUMBER: LDA2B209730D010 EU2B20WFL559730 2LBAD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P280963

CATALOG NUMBER: LDA2B209730D010 EU2B20WFL559730 2LBAD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95	95	95	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90	90	90	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72	72	72	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	65	65	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62	62	62	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1357189
5°	1329538
10°	1236350
15°	1079503
20°	893749
25°	683559
30°	374055
35°	138465
40°	47916
45°	21629
50°	10208
55°	5075
60°	1480
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P280963

CATALOG NUMBER: LDA2B209730D010 EU2B20WFL559730 2LBAD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.5	15.7
10°-20°	584.1	36.8
20°-30°	552.1	34.7
30°-40°	170.0	10.7
40°-50°	26.9	1.7
50°-60°	5.7	0.4
60°-70°	0.8	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1385.7	87.2
0°-40°	1555.7	97.9
0°-60°	1588.2	99.9
0°-90°	1589.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1589.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2751	
5°	2685	249
15°	2114	584
25°	1256	552
35°	230	170
45°	31	27
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280963

CATALOG NUMBER: LDA2B209730D010 EU2B20WFL559730 2LBAD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2750.9
1°	2740.6
2°	2728.1
3°	2717.7
4°	2704.5
5°	2684.6
6°	2658.8
7°	2624.1
8°	2577.7
9°	2523.9
10°	2467.9
11°	2406.0
12°	2340.4
13°	2269.0
14°	2194.5
15°	2113.5
17.5°	1899.0
20°	1702.3
22.5°	1502.6
25°	1255.7
27.5°	958.0
30°	656.6
32.5°	403.1
35°	229.9
37.5°	128.2
40°	74.4
42.5°	46.4
45°	31.0
47.5°	20.6
50°	13.3
52.5°	8.8
55°	5.9
57.5°	3.7
60°	1.5
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280963

CATALOG NUMBER: LDA2B209730D010 EU2B20WFL559730 2LBAD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)