

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280211

Luminaire Tested: **LDA2B059030D010 EU2B05WFL559030 2LBAD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280211
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059030D010 EU2B05WFL559030 2LBAD1LI
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 688.4 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280211

CATALOG NUMBER: LDA2B059030D010 EU2B05WFL559030 2LBAD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P280211

CATALOG NUMBER: LDA2B059030D010 EU2B05WFL559030 2LBAD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	587939
5°	575972
10°	535590
15°	467657
20°	387153
25°	296134
30°	162018
35°	59987
40°	20738
45°	9349
50°	4375
55°	2236
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P280211

CATALOG NUMBER: LDA2B059030D010 EU2B05WFL559030 2LBAD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.1	15.7
10°-20°	253.1	36.8
20°-30°	239.2	34.7
30°-40°	73.6	10.7
40°-50°	11.6	1.7
50°-60°	2.5	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	600.3	87.2
0°-40°	673.9	97.9
0°-60°	688.0	99.9
0°-90°	688.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	688.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1192	
5°	1163	108
15°	916	253
25°	544	239
35°	100	74
45°	13	12
55°	3	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280211

CATALOG NUMBER: LDA2B059030D010 EU2B05WFL559030 2LBAD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1191.7
1°	1187.2
2°	1181.8
3°	1177.3
4°	1171.6
5°	1163.0
6°	1151.8
7°	1136.8
8°	1116.7
9°	1093.4
10°	1069.1
11°	1042.3
12°	1013.9
13°	982.9
14°	950.7
15°	915.6
17.5°	822.7
20°	737.4
22.5°	650.9
25°	544.0
27.5°	415.0
30°	284.4
32.5°	174.6
35°	99.6
37.5°	55.5
40°	32.2
42.5°	20.1
45°	13.4
47.5°	8.9
50°	5.7
52.5°	3.8
55°	2.6
57.5°	1.6
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280211

CATALOG NUMBER: LDA2B059030D010 EU2B05WFL559030 2LBAD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)