

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P314916

Luminaire Tested: **LDA2B05NFL9030D010 PINW1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P314916
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B05NFL9030D010 PINW1MMS
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, White oculus, matte metallic silver finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 589.1 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314916

CATALOG NUMBER: LDA2B05NFL9030D010 PINW1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P314916

CATALOG NUMBER: LDA2B05NFL9030D010 PINW1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10		0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	99	97
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	96	96	96	96	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1507812
5°	1390602
10°	937069
15°	462039
20°	197357
25°	77572
30°	30535
35°	13371
40°	6440
45°	3070
50°	1689
55°	946
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P314916

CATALOG NUMBER: LDA2B05NFL9030D010 PINW1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.8	40.4
10°-20°	256.2	43.5
20°-30°	74.0	12.6
30°-40°	15.6	2.6
40°-50°	3.8	0.6
50°-60°	1.1	0.2
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	568.0	96.4
0°-40°	583.6	99.1
0°-60°	588.5	99.9
0°-90°	589.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	589.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3056	
5°	2808	238
15°	905	256
25°	142	74
35°	22	16
45°	4	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P314916

CATALOG NUMBER: LDA2B05NFL9030D010 PINW1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3056.2
1°	3037.0
2°	3004.5
3°	2960.6
4°	2898.4
5°	2807.9
6°	2685.6
7°	2526.1
8°	2330.0
9°	2101.4
10°	1870.5
11°	1637.1
12°	1416.8
13°	1221.3
14°	1049.3
15°	904.6
17.5°	597.9
20°	375.9
22.5°	231.1
25°	142.5
27.5°	87.0
30°	53.6
32.5°	33.9
35°	22.2
37.5°	14.7
40°	10.0
42.5°	6.9
45°	4.4
47.5°	2.8
50°	2.2
52.5°	1.7
55°	1.1
57.5°	0.8
60°	0.6
62.5°	0.6
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.3
80°	0.0
82.5°	0.0



TEST NUMBER: P314916

CATALOG NUMBER: LDA2B05NFL9030D010 PINW1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)