

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280101

Luminaire Tested: **LDA2B058027D010 EU2B05WFL558027 2LBAD1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280101
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B058027D010 EU2B05WFL558027 2LBAD1B
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, B
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 828.8 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280101

CATALOG NUMBER: LDA2B058027D010 EU2B05WFL558027 2LBAD1B

Luminous Intensity Polar Plot





TEST NUMBER: P280101

CATALOG NUMBER: LDA2B058027D010 EU2B05WFL558027 2LBAD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	707875
5°	693444
10°	644852
15°	563017
20°	466117
25°	356504
30°	195117
35°	72214
40°	24989
45°	11233
50°	5296
55°	2666
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P280101

CATALOG NUMBER: LDA2B058027D010 EU2B05WFL558027 2LBAD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.1	15.7
10°-20°	304.7	36.8
20°-30°	288.0	34.7
30°-40°	88.6	10.7
40°-50°	14.0	1.7
50°-60°	3.0	0.4
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	722.7	87.2
0°-40°	811.4	97.9
0°-60°	828.3	99.9
0°-90°	828.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	828.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1435	
5°	1400	130
15°	1102	305
25°	655	288
35°	120	89
45°	16	14
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280101

CATALOG NUMBER: LDA2B058027D010 EU2B05WFL558027 2LBAD1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1434.8
1°	1429.4
2°	1422.8
3°	1417.5
4°	1410.5
5°	1400.2
6°	1386.7
7°	1368.7
8°	1344.4
9°	1316.4
10°	1287.2
11°	1254.9
12°	1220.7
13°	1183.4
14°	1144.6
15°	1102.3
17.5°	990.5
20°	887.8
22.5°	783.7
25°	654.9
27.5°	499.6
30°	342.5
32.5°	210.2
35°	119.9
37.5°	66.9
40°	38.8
42.5°	24.2
45°	16.1
47.5°	10.8
50°	6.9
52.5°	4.6
55°	3.1
57.5°	1.9
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280101

CATALOG NUMBER: LDA2B058027D010 EU2B05WFL558027 2LBAD1B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)