

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278445

Luminaire Tested: **LDA2B059035D010 EU2B05NFL259035 2LBALD1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278445
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059035D010 EU2B05NFL259035 2LBALD1B
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, B
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 651.5 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278445

CATALOG NUMBER: LDA2B059035D010 EU2B05NFL259035 2LBALD1B

Luminous Intensity Polar Plot





TEST NUMBER: P278445

CATALOG NUMBER: LDA2B059035D010 EU2B05NFL259035 2LBALD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76	76	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1667612
5°	1537938
10°	1036362
15°	510970
20°	218253
25°	85792
30°	33782
35°	14816
40°	7149
45°	3419
50°	1919
55°	1032
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P278445

CATALOG NUMBER: LDA2B059035D010 EU2B05NFL259035 2LBALD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.1	40.4
10°-20°	283.3	43.5
20°-30°	81.8	12.6
30°-40°	17.3	2.7
40°-50°	4.3	0.7
50°-60°	1.2	0.2
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.1	96.4
0°-40°	645.4	99.1
0°-60°	650.9	99.9
0°-90°	651.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	651.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3380	
5°	3105	263
15°	1000	283
25°	158	82
35°	25	17
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278445

CATALOG NUMBER: LDA2B059035D010 EU2B05NFL259035 2LBALD1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3380.1
1°	3358.9
2°	3323.0
3°	3274.4
4°	3205.6
5°	3105.4
6°	2970.2
7°	2793.9
8°	2576.9
9°	2324.1
10°	2068.7
11°	1810.7
12°	1567.0
13°	1350.7
14°	1160.5
15°	1000.4
17.5°	661.2
20°	415.7
22.5°	255.6
25°	157.6
27.5°	96.2
30°	59.3
32.5°	37.5
35°	24.6
37.5°	16.3
40°	11.1
42.5°	7.7
45°	4.9
47.5°	3.1
50°	2.5
52.5°	1.8
55°	1.2
57.5°	0.9
60°	0.6
62.5°	0.6
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.3
80°	0.0
82.5°	0.0



TEST NUMBER: P278445

CATALOG NUMBER: LDA2B059035D010 EU2B05NFL259035 2LBALD1B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)