

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P491732

Luminaire Tested: **LDA2B058027R65D010 2LBD1GPH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P491732  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B058027R65D010 2LBD1GPH  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 772.5 lumens  
Efficiency: N/A  
Efficacy: 110.4 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P491732

CATALOG NUMBER: LDA2B058027R65D010 2LBD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P491732

CATALOG NUMBER: LDA2B058027R65D010 2LBD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67	74	70	66	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54	62	58	54	61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	419703
5°	385995
10°	368866
15°	354267
20°	326303
25°	302177
30°	276867
35°	203331
40°	96284
45°	31676
50°	10285
55°	1290
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P491732

CATALOG NUMBER: LDA2B058027R65D010 2LBD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.2	9.5
10°-20°	192.9	25.0
20°-30°	255.9	33.1
30°-40°	202.4	26.2
40°-50°	44.2	5.7
50°-60°	3.3	0.4
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	522.0	67.6
0°-40°	724.4	93.8
0°-60°	771.9	99.9
0°-90°	772.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	772.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	851	
5°	779	73
15°	694	193
25°	555	256
35°	338	202
45°	45	44
55°	2	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P491732

CATALOG NUMBER: LDA2B058027R65D010 2LBD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	850.7
1°	846.2
2°	830.5
3°	813.4
4°	795.4
5°	779.4
6°	769.1
7°	758.8
8°	751.9
9°	741.6
10°	736.3
11°	727.9
12°	718.4
13°	710.0
14°	700.4
15°	693.6
16°	676.0
17°	667.2
18°	652.7
19°	639.4
20°	621.5
21°	607.0
22.5°	587.9
23°	582.5
24°	568.1
25°	555.1
26°	547.1
27°	533.7
28°	520.7
29°	505.1
30°	486.0
32.5°	419.6
35°	337.6
37.5°	240.7
40°	149.5
42.5°	84.3
45°	45.4
47.5°	24.4
50°	13.4
52.5°	5.7
55°	1.5
57.5°	0.8
60°	0.8
62.5°	0.4
65°	0.4



TEST NUMBER: P491732

CATALOG NUMBER: LDA2B058027R65D010 2LBD1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)