

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P277925

Luminaire Tested: **LDA2B059035D010 EU2B05SP159035 2LBAD1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P277925
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059035D010 EU2B05SP159035 2LBAD1B
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, B
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 666.9 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P277925

CATALOG NUMBER: LDA2B059035D010 EU2B05SP159035 2LBAD1B

Luminous Intensity Polar Plot





TEST NUMBER: P277925

CATALOG NUMBER: LDA2B059035D010 EU2B05SP159035 2LBAD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98			98
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96			96
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93			93
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92			92
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90			90
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88			88
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86			86
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85			85
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83			83
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82			82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3012664
5°	2401895
10°	1042775
15°	360294
20°	147742
25°	66739
30°	26832
35°	12527
40°	6762
45°	2512
50°	1535
55°	1118
60°	691
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P277925

CATALOG NUMBER: LDA2B059035D010 EU2B05SP159035 2LBAD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.5	55.0
10°-20°	220.1	33.0
20°-30°	60.6	9.1
30°-40°	14.4	2.2
40°-50°	3.5	0.5
50°-60°	1.2	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	647.2	97.1
0°-40°	661.7	99.2
0°-60°	666.4	99.9
0°-90°	666.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	666.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6106	
5°	4850	367
15°	705	220
25°	123	61
35°	21	14
45°	4	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P277925

CATALOG NUMBER: LDA2B059035D010 EU2B05SP159035 2LBAD1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	6106.4
1°	6038.9
2°	5877.1
3°	5630.4
4°	5282.1
5°	4849.9
6°	4322.1
7°	3743.9
8°	3136.4
9°	2577.6
10°	2081.5
11°	1661.4
12°	1322.4
13°	1066.4
14°	862.8
15°	705.4
17.5°	437.8
20°	281.4
22.5°	184.5
25°	122.6
27.5°	78.7
30°	47.1
32.5°	29.7
35°	20.8
37.5°	15.2
40°	10.5
42.5°	6.3
45°	3.6
47.5°	2.6
50°	2.0
52.5°	1.6
55°	1.3
57.5°	1.0
60°	0.7
62.5°	0.7
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P277925

CATALOG NUMBER: LDA2B059035D010 EU2B05SP159035 2LBAD1B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)