

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P491759

Luminaire Tested: **LDA2B058027R70D010 2LBD1MMS**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P491759  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B058027R70D010 2LBD1MMS  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 748.1 lumens  
Efficiency: N/A  
Efficacy: 106.9 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P491759

CATALOG NUMBER: LDA2B058027R70D010 2LBD1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P491759

CATALOG NUMBER: LDA2B058027R70D010 2LBD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58		67	62	58		66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54		62	57	54		61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50		59	54	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	292317
5°	289075
10°	287659
15°	286642
20°	276425
25°	264997
30°	262340
35°	224049
40°	139821
45°	64679
50°	23410
55°	1634
60°	789
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P491759

CATALOG NUMBER: LDA2B058027R70D010 2LBD1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.4	7.4
10°-20°	157.2	21.0
20°-30°	226.0	30.2
30°-40°	222.8	29.8
40°-50°	79.4	10.6
50°-60°	6.5	0.9
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	438.5	58.6
0°-40°	661.3	88.4
0°-60°	747.2	99.9
0°-90°	748.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	748.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	592	
5°	584	55
15°	561	157
25°	487	226
35°	372	223
45°	93	79
55°	2	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P491759

CATALOG NUMBER: LDA2B058027R70D010 2LBD1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	592.5
1°	592.5
2°	591.3
3°	591.7
4°	586.7
5°	583.7
6°	579.5
7°	578.0
8°	576.1
9°	575.7
10°	574.2
11°	572.2
12°	572.2
13°	568.8
14°	564.2
15°	561.2
16°	555.1
17°	551.6
18°	541.0
19°	533.7
20°	526.5
21°	516.9
22.5°	503.6
23°	498.2
24°	493.3
25°	486.8
26°	483.0
27°	476.5
28°	475.7
29°	468.9
30°	460.5
32.5°	428.0
35°	372.0
37.5°	299.1
40°	217.1
42.5°	148.4
45°	92.7
47.5°	55.3
50°	30.5
52.5°	11.4
55°	1.9
57.5°	1.1
60°	0.8
62.5°	0.8
65°	0.8



TEST NUMBER: P491759

CATALOG NUMBER: LDA2B058027R70D010 2LBD1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)