

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P493910

Luminaire Tested: **LDA2B059050R65D010 2LBDL1WMH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P493910
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B059050R65D010 2LBDL1WMH
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 639.5 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P493910

CATALOG NUMBER: LDA2B059050R65D010 2LBDL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P493910

CATALOG NUMBER: LDA2B059050R65D010 2LBDL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93					93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87					87			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80					80			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74					74			
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69					69			
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64					64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60					60			
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56					56			
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	53	52					52			
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49					49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	334598
5°	320622
10°	305343
15°	290217
20°	269968
25°	249210
30°	216252
35°	155148
40°	84305
45°	36002
50°	15504
55°	5591
60°	987
65°	817
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P493910

CATALOG NUMBER: LDA2B059050R65D010 2LBDL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.6	9.5
10°-20°	159.2	24.9
20°-30°	208.1	32.5
30°-40°	158.3	24.8
40°-50°	45.8	7.2
50°-60°	6.9	1.1
60°-70°	0.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	427.9	66.9
0°-40°	586.2	91.7
0°-60°	638.8	99.9
0°-90°	639.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	639.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	678	
5°	647	61
15°	568	159
25°	458	208
35°	258	158
45°	52	46
55°	6	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P493910

CATALOG NUMBER: LDA2B059050R65D010 2LBDL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	678.2
1°	675.8
2°	672.0
3°	664.5
4°	656.3
5°	647.4
6°	638.9
7°	631.4
8°	624.2
9°	617.7
10°	609.5
11°	602.3
12°	594.8
13°	587.3
14°	579.1
15°	568.2
16°	560.0
17°	550.1
18°	535.0
19°	527.2
20°	514.2
21°	502.6
22.5°	484.8
23°	478.0
24°	467.4
25°	457.8
26°	445.2
27°	431.2
28°	415.8
29°	399.4
30°	379.6
32.5°	325.2
35°	257.6
37.5°	190.0
40°	130.9
42.5°	83.0
45°	51.6
47.5°	32.1
50°	20.2
52.5°	12.0
55°	6.5
57.5°	2.4
60°	1.0
62.5°	0.7
65°	0.7



TEST NUMBER: P493910

CATALOG NUMBER: LDA2B059050R65D010 2LBDL1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)