

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P314873

Luminaire Tested: **LDA2B05NFL8027D010 PIN1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P314873
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B05NFL8027D010 PIN1MMS
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, Black oculus, matte metallic silver finish
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 708.8 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314873
CATALOG NUMBER: LDA2B05NFL8027D010 PIN1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P314873

CATALOG NUMBER: LDA2B05NFL8027D010 PIN1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100															
	1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97	97	97	97	97	97	97	97	97															
	2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94	94	94	94	94	94	94	94	94															
	3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91	91	91	91	91	91	91	91	91															
	4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89															
	5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86	86	86	86	86	86	86	86	86															
	6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84	84	84	84	84	84	84	84	84	84														
	7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82	82	82	82	82	82	82	82	82	82														
	8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80	80	80	80	80	80	80	80	80	80														
	9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78	78	78	78	78	78	78	78	78														
	10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76	76	76	76	76	76	76	76	76	76	76	76	76														

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1814338
5°	1673239
10°	1127539
15°	555917
20°	237469
25°	93359
30°	36745
35°	16081
40°	7728
45°	3698
50°	2072
55°	1118
60°	691
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P314873

CATALOG NUMBER: LDA2B05NFL8027D010 PIN1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.2	40.4
10°-20°	308.2	43.5
20°-30°	89.0	12.6
30°-40°	18.8	2.6
40°-50°	4.6	0.7
50°-60°	1.3	0.2
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	683.4	96.4
0°-40°	702.2	99.1
0°-60°	708.1	99.9
0°-90°	708.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	708.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3678	
5°	3379	286
15°	1088	308
25°	172	89
35°	27	19
45°	5	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P314873

CATALOG NUMBER: LDA2B05NFL8027D010 PIN1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3677.5
1°	3654.4
2°	3615.3
3°	3562.5
4°	3487.6
5°	3378.6
6°	3231.5
7°	3039.6
8°	2803.6
9°	2528.5
10°	2250.7
11°	1969.9
12°	1704.9
13°	1469.5
14°	1262.6
15°	1088.4
17.5°	719.4
20°	452.3
22.5°	278.1
25°	171.5
27.5°	104.6
30°	64.5
32.5°	40.8
35°	26.7
37.5°	17.7
40°	12.0
42.5°	8.4
45°	5.3
47.5°	3.3
50°	2.7
52.5°	2.0
55°	1.3
57.5°	1.0
60°	0.7
62.5°	0.7
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.3
80°	0.0
82.5°	0.0



TEST NUMBER: P314873

CATALOG NUMBER: LDA2B05NFL8027D010 PIN1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)