

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279230

Luminaire Tested: **LDA2B058030D010 EU2B05FL408030 2LBALD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279230  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B058030D010 EU2B05FL408030 2LBALD1WMH  
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in ADJ spun Refl w/lens Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 839.7 lumens  
Efficiency: N/A  
Efficacy: 120.0 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279230

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P279230

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96													96															
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92													92															
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89													89															
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85													85															
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82													82															
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79													79															
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77													77															
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74													74															
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72													72															
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69													69															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1154516
5°	1130103
10°	1030000
15°	804609
20°	476407
25°	177082
30°	55316
35°	24633
40°	11399
45°	5372
50°	2993
55°	1634
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P279230

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	210.9	25.1
10°-20°	419.5	50.0
20°-30°	171.8	20.5
30°-40°	28.4	3.4
40°-50°	6.7	0.8
50°-60°	1.8	0.2
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	802.2	95.5
0°-40°	830.6	98.9
0°-60°	839.2	99.9
0°-90°	839.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	839.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2340	
5°	2282	211
15°	1575	419
25°	325	172
35°	41	28
45°	8	7
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279230

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2340.1
1°	2332.0
2°	2321.2
3°	2311.6
4°	2298.8
5°	2281.9
6°	2256.8
7°	2224.1
8°	2177.4
9°	2120.8
10°	2056.0
11°	1980.8
12°	1896.0
13°	1799.3
14°	1691.7
15°	1575.3
17.5°	1249.3
20°	907.4
22.5°	580.9
25°	325.3
27.5°	171.5
30°	97.1
32.5°	61.7
35°	40.9
37.5°	27.0
40°	17.7
42.5°	11.6
45°	7.7
47.5°	5.4
50°	3.9
52.5°	2.7
55°	1.9
57.5°	1.2
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279230

CATALOG NUMBER: LDA2B058030D010 EU2B05FL408030 2LBALD1WMH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)