

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P491819

Luminaire Tested: **LDA2B058030R20D010 2LBDLC1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P491819
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058030R20D010 2LBDLC1MW
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 797.5 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.34
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P491819

CATALOG NUMBER: LDA2B058030R20D010 2LBDLC1MW

Luminous Intensity Polar Plot





TEST NUMBER: P491819

CATALOG NUMBER: LDA2B058030R20D010 2LBDLC1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	105	104	103	102	102	100	100	99	99	97	97	97	97
2	112	109	106	104	110	107	105	102	104	102	100	100	101	100	98	98	98	97	96	96	95	95	95	95
3	109	105	101	99	107	103	100	98	101	98	96	96	99	97	95	95	97	95	94	94	92	92	92	92
4	106	101	98	95	104	100	97	94	98	95	93	93	96	94	92	92	95	93	91	91	90	90	90	90
5	103	98	94	92	102	97	94	91	96	93	90	90	94	92	90	90	93	91	89	89	88	88	88	88
6	101	95	91	89	100	95	91	88	93	90	88	88	92	89	87	87	91	89	87	87	86	86	86	86
7	98	93	89	86	97	92	89	86	91	88	86	86	90	87	85	85	89	87	85	85	84	84	84	84
8	96	90	87	84	95	90	86	84	89	86	84	84	88	85	83	83	87	85	83	83	82	82	82	82
9	94	88	85	82	93	88	84	82	87	84	82	82	86	84	82	82	86	83	81	81	81	81	81	81
10	92	86	83	80	91	86	83	80	85	82	80	80	85	82	80	80	84	82	80	80	79	79	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2636427
5°	2228410
10°	1357786
15°	558624
20°	201137
25°	80675
30°	36631
35°	17225
40°	9081
45°	4954
50°	2840
55°	1462
60°	789
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P491819

CATALOG NUMBER: LDA2B058030R20D010 2LBDLC1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	371.2	46.5
10°-20°	321.0	40.3
20°-30°	77.4	9.7
30°-40°	19.8	2.5
40°-50°	6.0	0.7
50°-60°	1.7	0.2
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	769.6	96.5
0°-40°	789.4	99.0
0°-60°	797.1	100.0
0°-90°	797.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	797.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5344	
5°	4500	371
15°	1094	321
25°	148	77
35°	29	20
45°	7	6
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P491819

CATALOG NUMBER: LDA2B058030R20D010 2LBDLC1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5343.8
1°	5297.3
2°	5186.5
3°	5018.0
4°	4800.9
5°	4499.6
6°	4188.3
7°	3844.7
8°	3487.7
9°	3087.2
10°	2710.3
11°	2316.4
12°	1971.1
13°	1644.4
14°	1344.8
15°	1093.7
16°	886.1
17°	715.6
18°	577.3
19°	474.8
20°	383.1
22.5°	236.2
25°	148.2
27.5°	96.3
30°	64.3
32.5°	42.3
35°	28.6
37.5°	19.9
40°	14.1
42.5°	10.0
45°	7.1
47.5°	5.4
50°	3.7
52.5°	2.5
55°	1.7
57.5°	1.2
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P491819

CATALOG NUMBER: LDA2B058030R20D010 2LBDLC1MW

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)