

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280286

Luminaire Tested: **LDA2B059727D010 EU2B05WFL559727 2LBALD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280286
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059727D010 EU2B05WFL559727 2LBALD1WMH
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 586.4 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280286

CATALOG NUMBER: LDA2B059727D010 EU2B05WFL559727 2LBALD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P280286

CATALOG NUMBER: LDA2B059727D010 EU2B05WFL559727 2LBALD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95				
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90				
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85				
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80				
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76				
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72				
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69				
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65				
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62				
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	500812
5°	490591
10°	456236
15°	398346
20°	329768
25°	252259
30°	138035
35°	51074
40°	17711
45°	7954
50°	3761
55°	1892
60°	493
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P280286

CATALOG NUMBER: LDA2B059727D010 EU2B05WFL559727 2LBALD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.1	15.7
10°-20°	215.5	36.8
20°-30°	203.7	34.7
30°-40°	62.7	10.7
40°-50°	9.9	1.7
50°-60°	2.1	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	511.3	87.2
0°-40°	574.0	97.9
0°-60°	586.1	99.9
0°-90°	586.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	586.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1015	
5°	991	92
15°	780	216
25°	463	204
35°	85	63
45°	11	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280286

CATALOG NUMBER: LDA2B059727D010 EU2B05WFL559727 2LBALD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1015.1
1°	1011.3
2°	1006.7
3°	1002.9
4°	998.0
5°	990.6
6°	981.1
7°	968.3
8°	951.2
9°	931.3
10°	910.7
11°	887.8
12°	863.6
13°	837.3
14°	809.8
15°	779.9
17.5°	700.7
20°	628.1
22.5°	554.5
25°	463.4
27.5°	353.5
30°	242.3
32.5°	148.7
35°	84.8
37.5°	47.3
40°	27.5
42.5°	17.1
45°	11.4
47.5°	7.6
50°	4.9
52.5°	3.3
55°	2.2
57.5°	1.4
60°	0.5
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280286

CATALOG NUMBER: LDA2B059727D010 EU2B05WFL559727 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)