

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P491861

Luminaire Tested: **LDA2B058030R35D010 2LBD1GPH-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P491861
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058030R35D010 2LBD1GPH-30DEG TILT
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 552.6 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 3.16 / 0.51 / 1.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P491861

CATALOG NUMBER: LDA2B058030R35D010 2LBD1GPH-30DEG TILT

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P491861

CATALOG NUMBER: LDA2B058030R35D010 2LBD1GPH-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90					90			
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80					80			
3	97	89	83	77	95	87	82	77	85	80	75	82	78	74	80	76	73	71					71			
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63					63			
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56					56			
6	77	66	58	53	76	65	58	52	63	57	52	62	56	52	60	55	51	49					49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44					44			
8	67	54	47	42	65	54	46	41	53	46	41	51	45	41	50	45	41	39					39			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35					35			
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	9226	9226	9226
5°	28873	8073	5002
10°	123289	6813	3707
15°	398397	4954	2962
20°	821139	3045	2048
25°	1085681	1470	1252
30°	1164550	684	684
35°	1112900	482	241
40°	1039091	258	0
45°	918407	0	0
50°	652097	307	0
55°	233789	344	0
60°	36114	789	0
65°	1868	934	0
70°	0	1154	0
75°	0	1525	762
80°	0	2273	0
85°	0	4529	0



TEST NUMBER: P491861

CATALOG NUMBER: LDA2B058030R35D010 2LBD1GPH-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3.3	0.6
10°-20°	44.7	8.1
20°-30°	149.7	27.1
30°-40°	188.5	34.1
40°-50°	133.4	24.1
50°-60°	30.8	5.6
60°-70°	1.0	0.2
70°-80°	0.6	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	197.7	35.8
0°-40°	386.2	69.9
0°-60°	550.3	99.6
0°-90°	552.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	552.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	19	19	19	19	19	
5°	58	38	16	12	10	11
15°	780	138	10	7	6	257
25°	1994	218	3	3	2	899
35°	1848	128	1	1	0	1157
45°	1316	32	0	0	0	987
55°	272	2	0	0	0	308
65°	2	0	1	1	0	6
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P491861

CATALOG NUMBER: LDA2B058030R35D010 2LBD1GPH-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7
1°	23.3	22.6	21.4	19.4	17.5	16.7	16.7	15.6	15.6
2°	28.0	26.8	24.5	20.6	17.5	15.6	14.8	14.0	13.6
3°	36.2	33.1	28.0	22.2	17.1	14.8	14.4	12.4	12.4
4°	45.1	42.0	32.3	23.3	16.7	14.0	12.4	11.7	11.3
5°	58.3	51.3	38.1	24.5	16.3	13.2	11.7	10.5	10.1
6°	75.4	65.7	43.6	25.7	15.9	12.4	10.9	9.7	9.3
7°	94.9	81.7	50.2	26.8	15.2	11.7	10.1	9.3	8.9
8°	136.1	105.0	57.9	27.6	14.8	10.9	9.7	8.6	8.2
9°	182.0	135.7	66.5	28.8	14.0	10.5	8.9	8.2	7.8
10°	246.1	177.7	76.2	29.6	13.6	9.7	8.2	7.8	7.4
11°	309.9	229.8	88.3	29.9	12.8	8.6	8.2	7.8	7.4
12°	414.9	279.6	98.8	29.9	12.1	8.2	7.4	7.0	6.6
13°	539.3	365.1	113.9	30.3	10.9	7.8	7.0	6.6	6.6
14°	649.0	441.7	124.0	30.3	10.5	7.0	6.6	6.6	6.2
15°	780.0	516.4	137.7	29.9	9.7	6.6	6.6	6.2	5.8
16°	917.3	628.4	155.9	29.2	8.9	5.8	6.2	5.4	5.1
17°	1099.3	720.9	169.9	28.4	8.2	5.4	5.4	5.4	5.1
18°	1265.7	833.3	181.2	27.6	7.4	5.4	5.1	5.1	4.7
19°	1444.2	923.5	192.5	26.4	6.6	4.7	4.7	4.7	4.3
20°	1564.0	1034.4	204.9	25.3	5.8	4.3	4.7	4.3	3.9
21°	1715.6	1133.5	209.6	24.1	5.1	3.9	3.9	3.9	3.5
22.5°	1857.6	1265.3	217.0	21.8	4.3	3.1	3.5	3.1	3.1
23°	1879.3	1293.3	217.0	21.0	3.9	3.1	3.5	3.1	3.1
24°	1951.7	1369.9	219.7	19.4	3.1	2.7	3.1	2.7	2.7
25°	1994.4	1430.6	217.8	17.9	2.7	2.7	2.7	2.7	2.3
26°	2011.9	1447.3	213.1	16.7	2.3	2.3	2.7	2.3	1.9
27°	2030.2	1485.4	207.3	15.2	1.9	2.3	2.3	2.3	1.9
28°	2043.0	1490.1	201.4	14.0	1.6	1.9	2.3	1.9	1.9
29°	2047.3	1496.3	194.4	12.4	1.2	1.6	1.9	1.6	1.6
30°	2044.2	1495.1	184.3	11.3	1.2	1.6	1.6	1.6	1.2
32.5°	1984.7	1461.7	156.3	8.2	0.8	1.2	1.2	1.2	0.8
35°	1847.8	1384.7	127.5	5.4	0.8	0.8	0.8	0.8	0.4
37.5°	1739.7	1269.6	97.6	3.1	0.4	0.8	0.8	0.4	0.0
40°	1613.4	1102.8	70.4	1.9	0.4	0.4	0.4	0.0	0.0
42.5°	1485.0	932.9	47.8	0.8	0.0	0.4	0.4	0.0	0.0
45°	1316.3	714.3	31.5	0.4	0.0	0.4	0.0	0.0	0.0
47.5°	1107.1	518.7	21.4	0.0	0.0	0.4	0.0	0.0	0.0
50°	849.6	290.5	12.1	0.0	0.4	0.4	0.4	0.0	0.0
52.5°	560.0	145.0	4.7	0.0	0.4	0.4	0.4	0.0	0.0
55°	271.8	77.8	1.6	0.4	0.4	0.8	0.4	0.0	0.0
57.5°	128.3	30.3	0.4	0.4	0.8	0.8	0.4	0.0	0.0
60°	36.6	6.2	0.4	0.4	0.8	0.8	0.4	0.4	0.0
62.5°	5.1	0.8	0.4	0.8	0.8	0.8	0.8	0.4	0.0
65°	1.6	0.4	0.4	0.8	0.8	0.8	0.8	0.4	0.0



TEST NUMBER: P491861

CATALOG NUMBER: LDA2B058030R35D010 2LBD1GPH-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
67.5°	0.4	0.4	0.4	0.8	0.8	0.8	0.8	0.4	0.0
70°	0.0	0.4	0.4	0.8	0.8	0.8	0.8	0.4	0.0
72.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
75°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.4
77.5°	0.0	0.4	0.8	0.8	1.2	0.8	0.8	0.4	0.0
80°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
82.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
85°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
87.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)