

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P493951

Luminaire Tested: **LDA2B059727R20D010 2LBD1WH-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P493951  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059727R20D010 2LBD1WH-30DEG TILT  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 352.8 lumens  
Efficiency: N/A  
Efficacy: 50.4 lumens/watt  
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P493951

CATALOG NUMBER: LDA2B059727R20D010 2LBD1WH-30DEG TILT

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P493951

CATALOG NUMBER: LDA2B059727R20D010 2LBD1WH-30DEG TILT

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91					91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82					82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74					74			
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66					66			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53					53			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48					48			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43					43			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38					38			
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34					34			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	5624	5624	5624
5°	10697	4952	3615
10°	25600	4358	2455
15°	149195	3473	970
20°	744327	2153	263
25°	1357264	762	0
30°	1591871	0	0
35°	1393323	0	0
40°	1028915	0	0
45°	370838	0	0
50°	77214	0	0
55°	17719	258	0
60°	5624	296	0
65°	1284	584	0
70°	0	721	433
75°	0	953	0
80°	0	1421	0
85°	0	2830	0



TEST NUMBER: P493951

CATALOG NUMBER: LDA2B059727R20D010 2LBD1WH-30DEG TILT

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1.3	0.4
10°-20°	19.4	5.5
20°-30°	130.7	37.0
30°-40°	152.6	43.3
40°-50°	44.5	12.6
50°-60°	3.0	0.8
60°-70°	0.5	0.2
70°-80°	0.4	0.1
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	151.3	42.9
0°-40°	304.0	86.2
0°-60°	351.5	99.6
0°-90°	352.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	352.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	11	11	11	11	11	
5°	22	16	10	8	7	3
15°	292	33	7	4	2	152
25°	2493	51	1	0	0	1104
35°	2313	28	0	0	0	1421
45°	532	6	0	0	0	490
55°	21	1	0	0	0	26
65°	1	0	0	0	0	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P493951

CATALOG NUMBER: LDA2B059727R20D010 2LBD1WH-30DEG TILT

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
2.5°	14.6	14.6	13.0	11.6	10.5	10.0	9.7	9.2	8.9
5°	21.6	18.9	15.7	12.2	10.0	9.2	8.4	7.6	7.3
7.5°	31.6	27.6	18.9	12.4	9.5	8.1	7.3	6.5	6.0
10°	51.1	39.8	23.3	12.4	8.7	7.0	6.0	5.1	4.9
12.5°	94.4	60.9	27.9	12.2	7.8	6.0	4.6	4.1	3.2
15°	292.1	126.1	33.0	11.6	6.8	4.6	3.5	2.2	1.9
17.5°	755.5	294.3	36.8	10.3	5.4	3.2	1.6	1.4	1.4
20°	1417.7	533.7	42.2	8.9	4.1	2.2	1.1	0.8	0.5
21°	1617.4	653.0	44.9	8.4	3.5	1.4	0.8	0.3	0.3
22°	1927.6	783.1	47.1	7.8	3.0	0.8	0.5	0.3	0.0
23°	2148.6	866.2	49.2	7.0	2.2	0.8	0.3	0.0	0.0
24°	2369.6	971.9	50.6	6.5	1.9	0.5	0.3	0.0	0.0
25°	2493.3	1060.1	51.1	6.0	1.4	0.3	0.0	0.0	0.0
26°	2595.0	1119.1	51.4	5.4	0.8	0.0	0.0	0.0	0.0
27°	2682.1	1187.5	50.9	4.9	0.8	0.0	0.0	0.0	0.0
28°	2731.6	1198.9	50.0	4.3	0.3	0.0	0.0	0.0	0.0
29°	2752.9	1185.1	47.6	3.8	0.3	0.0	0.0	0.0	0.0
30°	2794.3	1172.1	45.2	3.5	0.0	0.0	0.0	0.0	0.0
31°	2756.2	1129.1	42.2	3.0	0.0	0.0	0.0	0.0	0.0
32°	2606.9	1092.8	38.7	2.4	0.0	0.0	0.0	0.0	0.0
33°	2562.2	1018.5	34.9	2.2	0.0	0.0	0.0	0.0	0.0
34°	2478.1	907.8	31.6	1.9	0.0	0.0	0.0	0.0	0.0
35°	2313.4	816.4	27.6	1.6	0.0	0.0	0.0	0.0	0.0
36°	2198.4	712.0	24.1	1.4	0.0	0.0	0.0	0.0	0.0
37°	2078.0	620.8	21.4	1.1	0.0	0.0	0.0	0.0	0.0
38°	1928.4	525.1	18.1	0.8	0.0	0.0	0.0	0.0	0.0
39°	1754.2	433.9	15.4	0.8	0.0	0.0	0.0	0.0	0.0
40°	1597.6	349.8	13.3	0.5	0.0	0.0	0.0	0.0	0.0
42.5°	986.0	199.6	7.8	0.5	0.0	0.0	0.0	0.0	0.0
45°	531.5	121.2	5.7	0.3	0.0	0.0	0.0	0.0	0.0
47.5°	244.8	56.5	4.1	0.3	0.0	0.0	0.0	0.0	0.0
50°	100.6	25.2	3.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	36.2	14.1	1.9	0.0	0.0	0.3	0.0	0.0	0.0
55°	20.6	8.1	1.1	0.3	0.3	0.3	0.3	0.0	0.0
57.5°	9.7	4.6	0.3	0.3	0.3	0.3	0.3	0.0	0.0
60°	5.7	2.4	0.3	0.3	0.3	0.5	0.3	0.0	0.0
62.5°	2.7	0.8	0.3	0.5	0.5	0.5	0.5	0.3	0.0
65°	1.1	0.3	0.5	0.5	0.5	0.8	0.5	0.3	0.0
67.5°	0.3	0.3	0.5	0.5	0.5	0.8	0.5	0.3	0.3
70°	0.0	0.3	0.5	0.5	0.5	0.8	0.5	0.3	0.3
72.5°	0.0	0.3	0.5	0.5	0.5	0.8	0.5	0.3	0.3
75°	0.0	0.3	0.5	0.5	0.5	0.5	0.5	0.3	0.0
77.5°	0.0	0.3	0.5	0.5	0.5	0.5	0.5	0.3	0.0
80°	0.0	0.3	0.5	0.5	0.5	0.5	0.5	0.3	0.0



TEST NUMBER: P493951

CATALOG NUMBER: LDA2B059727R20D010 2LBD1WH-30DEG TILT

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.3	0.5	0.5	0.5	0.5	0.5	0.3	0.0
85°	0.0	0.3	0.5	0.5	0.5	0.5	0.5	0.3	0.0
87.5°	0.0	0.3	0.5	0.5	0.5	0.5	0.3	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)